

Features

- Rounded oak doors with curved metal edge detail
- Stainless steel sleigh legs
- Solid stainless steel door pulls
- Internal storage shelf
- Internal storage drawer with integrated handle
- Removable glass drawer dividers included

Materials & Construction


- Solid wood and veneer construction
- Stainless steel sleigh legs
- Full plywood back panel, no cutout
- Dovetailed drawers with solid oak front
- Blum undermount full extension slow close slides
- Blum slow close door hinges
- Durable, moisture resistant polyurethane finish
- Adjustable leveling feet

Options

- Available in:
 - CVBE6021587, Matte Black Oak paired with Aged Brass
 - CVBE6020169, Natural Grey paired with Brushed Pewter
- Engineered stone tops available:
 - TA60UCO93-8CS4
 - TA60UCO95-8CS4
 - TA60UCO96-8CS4
 - TA60UCO97-8CS4
 - TA60UCO98-8CS4
 - TA60UCO99-8CS4
 - TA60UCO100-8CS4
 - TA60UCO101-8CS4
- Coordinating mirrors available

Dimensions



Width: 59-7/8"
 Height: 32-7/8"
 Depth: 22-7/8"



Model Number Key

PRODUCT LINE	CATEGORY	COLLECTION	WIDTH	FINISH OPTIONS	OPTIONS
C = Craft Series	V = Vanity	BE = Bergman	60"	(See above)	(See above)

Bergman 60" Vanity CVBE60



Features

- Silestone Quartz Surface
- Includes Robern Ceramic Lavatory
- Includes installation hardware

Materials & Construction


- Pre-drilled for 8" wide spread faucet

Options

- Available finishes:
 - 93, White Zeus Extreme
 - 95, Eternal Marquina
 - 96, Pietra
 - 97, Calypso
 - 98, Eternal Serena
 - 99, Silken Pearl
 - 100, Eternal Calcatta Gold
 - 101, Iconic Black
- Pairs with Craft Series Bergman 60" vanity

Dimensions

Width: 60"
Height: 1-1/8"
Depth: 23"



Model Number Key

CATEGORY	DEPTH	WIDTH	LAV TYPE	OVERFLOW	COLORS	DASH	FAUCET HOLES	OPTIONS
T = Top	A = 23" Depth Fabricated Top	60"	U = Under Counter	D = Dual/Double Sink (60in Only)	(See above)	-	8 = 3 Holes Drilled (Centered on Lav Location)	(See above)

60" Top TA60UD0XXX-8CS4

