


Features

- Recess or surface mount
- Patented concealed surface-mounting system
- Mirrored doors and interior, matte silver interior
- Patented swing-out magnifying mirror
- Rust-free aluminum construction
- Three adjustable glass shelves
- Patented push button opener
- Polymer safety-back doors
- 3/4" (1.9 cm) Beveled mirrored doors and 1/4" (6 mm) beveled fascia
- 60" (152.4 cm) x 38-1/8" (96.8 cm) x 5-1/2" (14 cm)



Codes/Standards Applicable

Specified model meets or exceeds the following:

- None applicable

Specified Model

| Model | Description | |
|--|--|--------------------------|
| TFC6038 | Three door cabinet | <input type="checkbox"/> |
| Required Accessories - For Surface-Mount Installations Only | | |
| SK38 | Mirrored side kit (mounts to cabinet) | <input type="checkbox"/> |
| SKL38 | Mirrored side kit (mounts to cabinet with TLS light strip) | <input type="checkbox"/> |
| Optional Accessories | | |
| SLBTF60 | Safety-lock box | <input type="checkbox"/> |
| TLS60 | 15 bulb light strip | <input type="checkbox"/> |
| CAHC-A | Cabinet mounted halogen light, chrome and glass shade | <input type="checkbox"/> |
| CAHC-B | Cabinet mounted halogen light, all chrome shade | <input type="checkbox"/> |
| CAHC-CE | Cabinet mounted halogen light, ebony black shade | <input type="checkbox"/> |
| CAHC-CS | Cabinet mounted halogen light, matte silver shade | <input type="checkbox"/> |
| Cabinet cannot be recessed when using a CAHC light. Refer to the Price Guide for more information. | | |

C SERIES THREE DOOR CABINET

Technical Information

| | |
|---------------------|---|
| Roughing-in opening | 58-3/4" (149.2 cm) x 34-3/4" (88.3 cm) x 4" (10.2 cm) |
| Door opening angle | 180° |


Installation Notes

Install this product according to the installation guide.

When determining the height of the mirrored cabinet, ensure the mirrored door will clear all obstacles, such as a faucet. A minimum distance of 1" (2.5 cm) is required.

Secure the screws (provided) to a stud to avoid possible property and product damage. If this is not possible, anchors must be inserted before installing the screws.

Recessed cabinets project 1-7/8" (4.8 cm) from wall.



Product Diagram