



#### **Features**


- · Recess or surface mount
- Mirrored doors and interior, matte silver interior
- 3-way adjustable concealed hinge system
- SAFESEAL™ gasket frame
- Patented swing-out magnifying mirror
- Rust-free aluminum construction
- Left or right hinge door available
- Three adjustable glass shelves
- Layered glass creates a sophisticated showpiece
- Available in tinted gray mirror or tinted white glass
- Electric feature includes two duplex 15 A, 110 VAC GFCI outlets
- 19-1/4" (48.9 cm) x 30" (76.2 cm) x 5" (12.7 cm)



Specified model meets or exceeds the following:

· Electrical options are UL listed for damp locations

# WITH ELECTRIC MT20D4CDGRE ALSO MT20D4CDGLE, MT20D4CDWRE, MT20D4CDWLE



### **Specified Model**

Model	Description	
MT20D4CDGRE	Tinted gray mirror, right-hand, electric	
MT20D4CDGLE	Tinted gray mirror, left-hand, electric	
MT20D4CDWRE	White glass, right-hand, electric	
MT20D4CDWLE	White glass, left-hand, electric	
NOTE: Hardware required for installing cabinets side-by-side is included.		

Required Accessories - For Surface-Mount Installations Only		
MTSK30D4G	Tinted gray mirror side kit	
MTSK30D4W	White glass side kit	
Refer to the Price Guide for additional side kit colors and finishes		

Optional Accessories		
SLB20D4	Safety-lock box	
MLLWCDG	Candre™ single wall sconce with tinted gray mirror backplate	
MLLWCDW	Candre™ single wall sconce with white glass backplate	
Frames, light options, and additional accessories are also available. Refer to the Price Guide for more information.		

#### CANDRETM CABINET

#### **Technical Information**

Roughing-in opening	18-1/2" (47 cm) x 29-1/4" (74.3 cm) x 4" (10.2 cm)
Door opening angle	170°


#### **Installation Notes**

Install this product according to the installation guide.


When determining the height of the mirrored cabinet, ensure the mirrored door will clear all obstacles, such as a faucet. A minimum distance of 1" (2.5 cm) is required.

Secure the screws (provided) to a stud to avoid possible property and product damage. If this is not possible, anchors (provided) must be inserted before installing the screws.

Recessed cabinets project 1-1/4" (3.2 cm) from wall.



## Electrical Connection Detail (Rear View)



**Product Diagram** 

