

Features

- Metal Construction
- Includes installation hardware
- Complements Decorative glass vanities and cabinets
- 18-W or 26-W, 4-pin, G24Q-3 base single twin tube plug-in CFL bulb (not supplied) required
- This Sconce is designed to be noiseless and flicker-free up to 28 watts. Also, with End of Lamp Life (EOL) auto-reset protection circuit.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ETL certified (damp locations) to:
 - UL 1598
 - CSA C22.2 NO.250.0
- Complies with California Title 24 Section 6 energy requirements

Base Finishes

- CR=Chrome
- BN=Brushed Nickel

Glass Insert Finish

Stock Colors

- 10 - Mirror
- 11 - Tinted Gray Mirror
- 20 - Black
- 21 - White
- 22 - Beach

Special Order Colors


- 12 - Satin Bronze
- 19 - Satin White
- 23 - Ocean
- 24 - Smoke Screen
- 25 - Silver Screen

Digital Marble™

- 40 - Calacatta
- 41 - Nero

Digital Wood™

- 50 - Indian Rosewood
- 52 - European Ash
- 54 - Santos Rosewood
- 55 - Smooth-Leaved Elm
- 56 - Charcoal Ash
- 57 - Bleached Oak



Model Numbers

	D	L	F	DG	##	-	##
Product	D = Decorative						
Category	L = Light						
Type of Lamp	F = Fluorescent						
Style	DG = Decorative Glass						
Base Fixture Finish	CR = Chrome BN = Brushed Nickel						
Glass Insert Finish	## = Decorative glass & digital options						

Product Specification

The wall sconce shall be of metal construction. Product shall include installation hardware. Product shall require a 26-W, 4-pin, single twin tube plug-in CFL bulb (not supplied). Product shall complement vanities and cabinets.

Wall sconce shall be Robern Model D L F DG ____.

Installation Notes

- Install this product according to the installation guide.
- A 2700K - 3200K bulb is recommended for task lighting.
- If you are installing this sconce as grooming light, we recommend installing two sconces on either side of a mirror. Mount each sconce a maximum of 20" (508 mm) from the center of the mirror.
- Install only with a standard UL Listed junction box measuring 2-3/8" x 3-1/2" x 2-3/4" deep.
- If installed with a Robern cabinet or mirror, the center of the junction box should be located 3-3/4" (95 mm) above the center of the cabinet or mirror (see Figure 1).
- If installed with a Robern M Series Cabinet the Sconces should be installed with a center to center distance of at least the width of the cabinet + 10" (254 mm) (see Figure 1).
- The proper height of the cabinet depends upon the height of the user. Refer to the installation guide to determine the proper height of the sconce.

