

Features

- Rounded vanity frame with decorative parting line details
- Carved, integrated drawer pulls
- Top drawer is false front
- Bottom drawer is a plumbing drawer
- Minimalist floating installation
- Removable glass drawer dividers included

Materials & Construction


- Solid wood and veneer construction
- Full plywood back panel, no cutout
- Dovetailed drawers
- Blum undermount full extension slow close slides
- Durable, moisture resistant polyurethane finish
- Solid steel mounting brackets

Options

- Available in:
 CVHE36204, Rustic Oak
- Engineered stone tops available:
 TA36UCO93-8CS6
 TA36UCO95-8CS6
 TA36UCO96-8CS6
 TA36UCO97-8CS6
 TA36UCO98-8CS6
 TA36UCO99-8CS6
 TA36UCO100-8CS6
 TA36UCO101-8CS6
- Coordinating mirrors available




Dimensions

Width: 35"
 Height: 19-1/4"
 Depth: 22-1/2"



Model Number Key

PRODUCT LINE	CATEGORY	COLLECTION	WIDTH	FINISH OPTIONS	OPTIONS
C = Craft Series	V = Vanity	HE = Helden	36"	(See above)	(See above)



Internal
Construction

Features

- Silestone Quartz Surface
- Includes Robern Ceramic Lavatory
- Includes installation hardware

Materials & Construction


- Pre-drilled for 8" wide spread faucet

Options

- Available finishes:
 - 93, White Zeus Extreme
 - 95, Eternal Marquina
 - 96, Pietra
 - 97, Calypso
 - 98, Eternal Serena
 - 99, Silken Pearl
 - 100, Eternal Calcatta Gold
 - 101, Iconic Black
- Pairs with Craft Series Helden 36" vanity

Dimensions

Width: 36"
 Height: 1-1/8"
 Depth: 23"



Model Number Key

CATEGORY	DEPTH	WIDTH	LAV TYPE	OVERFLOW	COLORS	DASH	FAUCET HOLES	OPTIONS
T = Top	A = 23" Depth Fabricated Top	36"	U = Under Counter	C = Center Mounted	(See above)	-	8 = 3 Holes Drilled (Centered on Lav Location)	(See above)

36" Top TA36UCOXXX-8CS6

