

**Features**

- Rounded vanity frame with decorative parting line details
- Carved, integrated drawer pulls
- Top drawers are false front
- Bottom drawers are plumbing drawers
- Minimalist floating installation
- Removable glass drawer dividers included

**Materials & Construction**


- Solid wood and veneer construction
- Full plywood back panel, no cutout
- Dovetailed drawers
- Blum undermount full extension slow close slides
- Durable, moisture resistant polyurethane finish
- Solid steel mounting brackets

**Options**

- Available i:  
 CVHE60204, Rustic Oak
- Engineered stone tops available:  
 TA60UCO93-8CS7  
 TA60UCO95-8CS7  
 TA60UCO96-8CS7  
 TA60UCO97-8CS7  
 TA36UCO98-8CS7  
 TA36UCO99-8CS7  
 TA36UCO100-8CS7  
 TA36UCO101-8CS7
- Coordinating mirrors available




**Dimensions**

Width: 59"  
 Height: 19-1/4"  
 Depth: 22-1/2"



**Model Number Key**

PRODUCT LINE	CATEGORY	COLLECTION	WIDTH	FINISH OPTIONS	OPTIONS
C = Craft Series	V = Vanity	HE = Helden	60"	(See above)	(See above)



Internal Construction

### Features

- Silestone Quartz Surface
- Includes Robern Ceramic Lavatory
- Includes installation hardware

### Materials & Construction


- Pre-drilled for 8" wide spread faucet

### Options

- Available finishes:
  - 93, White Zeus Extreme
  - 95, Eternal Marquina
  - 96, Pietra
  - 97, Calypso
  - 98, Eternal Serena
  - 99, Silken Pearl
  - 100, Eternal Calcatta Gold
  - 101, Iconic Black
- Pairs with Craft Series Helden 60" vanity

### Dimensions

Width: 60"  
 Height: 1-1/8"  
 Depth: 23"



### Model Number Key

CATEGORY	DEPTH	WIDTH	LAV TYPE	OVERFLOW	COLORS	DASH	FAUCET HOLES	OPTIONS
T = Top	A = 23" Depth Fabricated Top	60"	U = Under Counter	D = Dual/Double Sink (60in Only)	(See above)	-	8 = 3 Holes Drilled (Centered on Lav Location)	(See above)

60" Top TA60UDOXXX-8CS7

