

### Features

- Three different ways to access the lock box:
  - Physical keys that cannot be duplicated
  - Access code via digital keypad
  - Remote unlock using Robern IQ Digital Lock Box app (available on iOS and Android)
- Receive notifications in your app about all lock box events
- Integrated tamper detection alerts users of unauthorized access attempts
- Easy installation and setup
- Suitable for damp environments
- Door gasket seals contents from moisture and dust

### Construction

- Anodized aluminum shelf
- Includes easy installation hardware
- Physical Entry Keys (set of two included)
- Requires four AA batteries (not included)



### Dimensions

IQ DLB Height: 5-3/4" (144.7 mm)  
 IQ DLB Width: 13-17/32" (344 mm)  
 IQ DLB Depth: 2-15/16" (74.6 mm)


Storage Height: 5-1/4" (133.4 mm)  
 Storage Width: 9" (228.6 mm)  
 Storage Depth: 2-7/16" (62 mm)

### Options

- Compatible cabinet lines by size:
  - DLB-16
    - M Series (MC16)
    - Portray (P2C16)\*
    - Profiles (PC16)
    - PL Series (PL16)
    - DC Series (DC16)
  - DLB-20
    - M Series (MC20)
    - Portray (P2C20)\*
    - Profiles (PC20)
    - PL Series (PL20)
    - DC Series (DC20)
  - DLB-24
    - M Series (MC24)
    - Portray (P2C24)\*
    - Profiles (PC24)
    - AiO (AC24)
    - Vitality (YC24)
    - PL Series (PL24)
    - DC Series (DC24)
  - DLB-R20
    - R<sup>3</sup> Series (RC20)\*
  - DLB-R24
    - R<sup>3</sup> Series (RC24)\*
  - DLB-UPLIFT24
    - Uplift Tech (UC24)\*
  - DLB-UPLIFT
    - Uplift Tech (UC30)\*
    - Uplift Tech (UC36)\*
    - Uplift Tech (UC48)\*




\*Installation does not require access to exterior of cabinet. Lock box installation height can be adjusted in 1" (25.4mm) increments.



Front view

IQ Lock box Shelf Width	
DLB-16	13-5/8" (346mm)
DLB-20	17-5/8" (447.7mm)
DLB-24	21-5/8" (549.3mm)
DLB-R20	16-21/32" (422.7mm)
DLB-R24	20-21/32" (524.3mm)
DLB-UPLIFT24	21-3/4" (552.5mm)
DLB-UPLIFT	18" (457.2mm)

Side view



Top view

