



MTL INCANDESCENT TOP LIGHT

Features

- Compatible with all 24" (61 cm) wide M Series cabinets
- Available with black or white accents
- Available with incandescent or fluorescent bulbs
- Easily mounts for a seamless look
- 23-1/4" (59.1 cm) x 3" (7.6 cm)

MTL24T
ALSO MTL24TW

Codes/Standards Applicable

Specified model meets or exceeds the following:

- UL listed for damp locations



Specified Model

Model	Description	
MTL24T	5 bulb black incandescent light	<input type="checkbox"/>
MTL24TW	5 bulb white incandescent light	<input type="checkbox"/>


MTL INCANDESCENT TOP LIGHT

Installation Notes

Install this product according to the installation guide.

Line voltage fixture uses G-16 1/2" candelabra base bulbs, 15 watt to 40 watt (Model # BULBCAN25 or 25F). Bulbs are not included.

Top lights are for use with 4" (10.2 cm) depth surface mount cabinets, 8" (20.3 cm) semi-recessed cabinets, and any fully recessed cabinet.



Product Diagram