

### Features

- Brightness - 600 Lux
- Multi-array LED system to evenly illuminate your face
- Color temperature: 4500 Kelvin
- 3 adjustable brightness settings
- Color Rendering Index (CRI) of 90+ to provide a full color spectrum
- LED lifespan >40000 hours (100+ years at 1 hour a day)
- Rechargeable via any standard USB port or optional Inductive Charging Dock\*
- Optional Inductive Charging Dock mounts inside your M Series cabinet with the E2 or E4 electric option\*

### Mirror

- 5X Magnification for up-close viewing and tasks like tweezing and applying makeup
- Distortion-free mirror

### Operation

- Auto-on functionality when coupled with the M Series or AIO® cabinet doors
- Attaches magnetically to M Series or AIO cabinet doors\*
- Push-button when utilized on vanity table or hand held

### Intelligent Power and Rechargeable Battery

- Utilizes integrated sensing technology for efficient battery life
- Up to 2 hours of lighting at the brightest setting
- 3.7V 3100mah Lithium-Ion battery
- Rechargeable via the supplied USB cord to port/adaptor (port/adaptor not included)

### Adjustability


- Adjustable height and angle when coupled with M Series or AIO cabinet doors\*
- Vanity table top or hand-held usability

### Mirror Dimensions

**Height:** 5-3/16" (132 mm)  
**Width:** 7-3/16" (183 mm)  
**Depth:** 1-13/16" (46 mm)  
**Weight:** 0.8 lbs (0.36 kg)

### Options

- Rechargeable via optional Inductive Charging Dock\*
- Optional Inductive Charging Dock mounts inside your M Series cabinet with the E2 or E4 electric option\*



\*Connections are made using a magnetic field.  
 ⚠️ ⚡ PACEMAKER WARNING: Strong magnet! Can be harmful to pacemaker wearers and others with medical implants.

## Entice Dimensions

