

### Features

- Metal Framed Mirrored Cabinet
- All cabinets are non-handed/reversible
- Mirrored interior with 4 adjustable, cantilevered glass shelves
- Cantilever shelving adjustable in 1" increments
- Includes installation hardware for recess mounting
- Can be recessed or surface mounted (surface mounting kit required)
- Blum 155° slow close hinges

### Optional Features & Upgrades

- PORTRAY Electric Upgrade (P2ELECTRIC - included with TM option)
- IQ™ Digital Lock Box (DLB or DLB-24)
- Other widths/heights available
- Glass Storage Bins (GLASSBIN3.25, GLASSBIN5.25, GLASSBIN8.5)

### Construction

- Rust free Satin anodized aluminum construction
- Blum hinges standard
- 3 mirror design - rear of cabinet and both sides of door

### Codes/Standards (Electrical Upgrade Only)

- Electric Option Models are ETL certified to:
  - UL 962
  - CSA Standard C22.2 No. 68

### Dimensions

Width: 23-3/8" (594 mm)  
 Height: 39-7/16" (1002 mm)  
 Depth: See page 2 for dimensions


### Installation Options

**Recessed Mount** - Rough Opening - 22-1/2" W x 38-5/8" H x 4" D  
 (571.5 mm W x 981 mm H x 102 mm D)


**Surface Mount (Single Cabinet)** - Reference Surface Mount Kit when ordering (P2SMKIT)

### Electrical Upgrade Only


- 120 VAC 60HZ 20A
- Field wire location as shown in drawing
- 1/2" conduit (Ø7/8" actual) electrical knockout location




(Merion Option Shown)



Bryn Mawr



Merion




Rosemont


See page 2 for frame dimensions.

### Model Number Key

Width	Height	Depth	Frame Style	Frame Finish	Package Option	
D2C	24	40	D4	BM = Bryn Mawr ME = Merion RM = Rosemont	66 = Nickel 67 = Vintage Brass 74 = Brushed Black 75 = Brushed Bronze 76 = Chrome 77 = Polished Nickel	SC = Slow-Close Hinges TM = Slow-Close Hinges, Sliding Magnification Mirror, Magnetic Strip, Interior Lighting, USB Charging Ports, Electrical Outlets, Phone Holder



Front View



Recess Mount

Surface Mount



Click or scan the QR code to see the rough opening and electrical details found in the Mainline Series cabinet installation instructions.

Use the camera app on your mobile device to look at this QR code. This will allow you to quickly access web pages and other relevant documents.

		Dimensions projected from wall		
		Recessed Mount		
		Bryn Mawr	Merion	Rosemont
A=				
		1-1/4" (32 mm)	1-1/4" (32 mm)	1-9/16" (40 mm)
		Surface Mount		
		Bryn Mawr	Merion	Rosemont
B=		5" (127 mm)	5" (127 mm)	5-5/16" (135 mm)