

Features


- Metal Framed Wall Mirror
- Color and style matched to Main Line cabinets
- Easy installation

Construction


- Rust-free aluminum construction, available in plated or anodized finishes
- Includes installation hardware

Dimensions


Width: 15-3/8" (390.5 mm)
 Height: 39-7/16" (1002 mm)
 Depth: See page 2 for dimensions




(Merion Option Shown)



Bryn Mawr



Merion




Rosemont

See page 2 for frame dimensions.

Model Number Key

	Width	Height	Frame Style	Frame Finish
DM	16	40	BM = Bryn Mawr ME = Merion RM = Rosemont	66 = Nickel 67 = Vintage Brass 74 = Brushed Black 75 = Brushed Bronze 76 = Chrome 77 = Polished Nickel



Click or scan the QR code to see the details found in the installation instructions.

Use the camera app on your mobile device to look at this QR code. This will allow you to quickly access web pages and other relevant documents.

Dimensions projected from wall			
Recessed Mount			
	Bryn Mawr	Merion	Rosemont
	15/16" (24 mm)	7/8" (22 mm)	1-3/16" (30 mm)
A=	15/16" (24 mm)	7/8" (22 mm)	1-3/16" (30 mm)