

#### **Features**

- · Recess or surface mount
- Ideal for remodeling: features 1" (2.5 cm) flange to hide gaps, paint lines or any wall imperfections
- · Slow-close functionality
- 108-degree in-set adjustable hinge
- · Clean interior due to "hidden" shelf adjustments and off-set door hinge (patent pending)
- · 3 Mirror construction: front of door, back of door and inside of cabinet
- · Low-profile laminated door design
- Thin door and off-set hinge allow for more storage than any cabinet of similar size
- Anodized aluminum construction
- · Can be installed as a left- or right-hand door swing
- Four adjustable, cantilever glass shelves
- 16" (40.6 cm) W x 36" (91.4 cm) H x 4-3/4" (12.1 cm) D


## Codes/Standards Applicable

Specified model meets or exceeds the following:

· None applicable

# RC1636D4FB1

ALSO RC1636D4FP1



# **Specified Model**

Model	Description		
RC1636D4FB1	Beveled edge		
RC1636D4FP1	Plain edge		
Required Accessories - For Surface Mount Installations Only			
RSMK36D4P	Plain mirror side kit with mounting hardware		

Page 1 of 2 1176661-4-A USA: 1-800-877-2376 www.robern.com

# R<sup>3</sup>™ SERIES FLAT DOOR CABINET

## **Technical Information**

Roughing-in opening	14" (35.6 cm) W x 34" (86.4 cm) H x 4" (10.2 cm) D
Door opening angle	108°


### **Installation Notes**

Install this product according to the installation guide.

When determining the height of the mirrored cabinet, ensure the mirrored door will clear all obstacles, such as a faucet. A minimum distance of 1" (2.5 cm) is required.

Secure the screws (provided) to a stud to avoid possible property and product damage. If this is not possible, anchors (provided) must be inserted before installing the screws.

Recessed cabinets project 1" (2.5 cm) from wall.



**Product Diagram** 

