

Features

- Includes mirror defogging
- Dimmable LED task lighting to 1%
- Front and side diffuser, no visible LEDs
- Energy efficient LED lighting

Lighting Specs

Kelvin:	3000K, 4000K
CRI:	90+
Lumens†:	740-1200
Lux†:	460-680
R9 Value:	50+
Foot-candles†:	42-63
Input Power – LED:	55w max
Input Power – LED with defogger on:	85w max

†Measured at 18" from center of mirror

Construction

- Anodized aluminum back frame
- Quality polished edge mirror
- Power cords installed for easy plugin installation
- Constructed for surface mounting
- Includes installation hardware


Dimensions

Diameter: 30" (762 mm), 40" (1016 mm)
Depth: 1-3/4" (45 mm)

Codes/Standards Applicable

Core Lighted Mirror is UL certified to:


- UL 962
- CSA-C22.2, No. 250.4




Savant Model Number	Product Description
SVTCM00030N03100	Core Lighted Mirrors, Diameter 30", 3000K, Inset Light Pattern
SVTCM00030N04100	Core Lighted Mirrors, Diameter 30", 4000K, Inset Light Pattern
SVTCM00040N03100	Core Lighted Mirrors, Diameter 40", 3000K, Inset Light Pattern
SVTCM00040N04100	Core Lighted Mirrors, Diameter 40", 4000K, Inset Light Pattern

Electrical System


- 120 VAC 60HZ wall outlet as shown in drawing



Back view for electrical outlet location



Side view



Front view

* Defogger Size

† See instructions for wiring and location