

Features

- Includes mirror defogging
- Dimmable LED task lighting to 1%
- Front and side diffuser, no visible LEDs
- Energy efficient LED lighting

Lighting Specs

Kelvin:	3000K
CRI:	90+
Lumens†:	1120-1480
Lux†:	280-330
R9 Value:	50+
Foot-candles†:	27-31
Input Power – LED:	55w max
Input Power – LED with defogger on:	85w max

†Measured at 18" from center of mirror

Construction

- Anodized aluminum back frame
- Quality polished edge mirror
- Power cords installed for easy plugin installation
- Constructed for surface mounting
- Includes installation hardware


Dimensions

- Diameter: 30" (762 mm), 40" (1016 mm)
- Depth: 1-3/4" (45 mm)

Codes/Standards Applicable

Core Lighted Mirror is UL certified to:

- UL 962
- CSA-C22.2, No. 250.4



Savant Model Number

Product Description

SVTCM00030N03P00


Core Lighted Mirrors, Diameter 30", 3000K, Perimeter Light Pattern

SVTCM00040N03P00

Core Lighted Mirrors, Diameter 40", 3000K, Perimeter Light Pattern

Electrical System

- 120 VAC 60HZ wall outlet as shown in drawing



* Defogger Size

* See instructions for wiring and location