

Features

- Includes mirror defogging
- Dimmable LED task lighting to 1%
- Front and side diffuser, no visible LEDs
- Energy efficient LED lighting

Lighting Specs

Kelvin:	3000K, 4000K
CRI:	90+
Lumens†:	810-1250
Lux†:	350-610
R9 Value†:	50+
Foot-candles†:	32-56
Input Power – LED:	55w max
Input Power – LED with defogger on:	85w max

†Measured at 18" from center of mirror

Construction

- Anodized aluminum back frame
- Quality polished edge mirror
- Power cords installed for easy plugin installation
- Constructed for surface mounting
- Includes installation hardware


Dimensions

- 24" x 30" x 1-3/4" (610 mm x 762 mm x 45 mm)
- 24" x 40" x 1-3/4" (610 mm x 1016 mm x 45 mm)
- 30" x 30" x 1-3/4" (762 mm x 762 mm x 45 mm)
- 30" x 40" x 1-3/4" (762 mm x 1016 mm x 45 mm)
- 36" x 30" x 1-3/4" (914 mm x 762 mm x 45 mm)
- 36" x 40" x 1-3/4" (914 mm x 1016 mm x 45 mm)
- 48" x 36" x 1-3/4" (1219 mm x 914 mm x 45 mm) – flip to be 36" x 48" x 1-3/4" (914 mm x 1219 mm x 45 mm)

Codes/Standards Applicable

Core Lighted Mirror is UL certified to:

- UL 962
- CSA-C22.2, No. 250.4




Savant Model Number	Product Description
SVTCM02430N03C00	Core Lighted Mirrors, 24" x 30", 3000K, Column Light Pattern
SVTCM02430N04C00	Core Lighted Mirrors, 24" x 30", 4000K, Column Light Pattern
SVTCM02440N03C00	Core Lighted Mirrors, 24" x 40", 3000K, Column Light Pattern
SVTCM02440N04C00	Core Lighted Mirrors, 24" x 40", 4000K, Column Light Pattern
SVTCM03030N03C00	Core Lighted Mirrors, 30" x 30", 3000K, Column Light Pattern
SVTCM03030N04C00	Core Lighted Mirrors, 30" x 30", 4000K, Column Light Pattern
SVTCM03040N03C00	Core Lighted Mirrors, 30" x 40", 3000K, Column Light Pattern
SVTCM03040N04C00	Core Lighted Mirrors, 30" x 40", 4000K, Column Light Pattern

Savant Model Number	Product Description
SVTCM03040N04C00	Core Lighted Mirrors, 30" x 40", 4000K, Column Light Pattern
SVTCM03630N03C00	Core Lighted Mirrors, 36" x 30", 3000K, Column Light Pattern
SVTCM03630N04C00	Core Lighted Mirrors, 36" x 30", 4000K, Column Light Pattern
SVTCM03640N03C00	Core Lighted Mirrors, 36" x 40", 3000K, Column Light Pattern
SVTCM03640N04C00	Core Lighted Mirrors, 36" x 40", 4000K, Column Light Pattern
SVTCM04836N03C00	Core Lighted Mirrors, 48" x 36", 3000K, Column Light Pattern
SVTCM04836N04C00	Core Lighted Mirrors, 48" x 36", 4000K, Column Light Pattern

Electrical System

- 120 VAC 60HZ wall outlet as shown in drawing



Dimensions						
A	B	C	D	E	F	G
12-3/16" (310 mm)	17-3/4" (450 mm)	9-1/8" (231 mm)	24" (610 mm)	16" (410 mm)	26" (661 mm)	30" (762 mm)
12-3/16" (310 mm)	17-3/4" (450 mm)	13-1/16" (332 mm)	24" (610 mm)	16" (410 mm)	36" (916 mm)	40" (1016 mm)
17-3/4" (450 mm)	12-3/16" (310 mm)	13-5/8" (346 mm)	30" (762 mm)	22" (560 mm)	26" (661 mm)	30" (762 mm)
12-3/16" (310 mm)	17-3/4" (450 mm)	15-1/16" (383 mm)	30" (762 mm)	22" (560 mm)	36" (916 mm)	40" (1016 mm)
17-3/4" (450 mm)	12-3/16" (310 mm)	14-1/8" (359 mm)	36" (914 mm)	28" (711 mm)	26" (661 mm)	30" (762 mm)
17-3/4" (450 mm)	12-3/16" (310 mm)	16-5/16" (415 mm)	36" (915 mm)	28" (711 mm)	36" (914 mm)	40" (1016 mm)
17-3/4" (450 mm)	12-3/16" (310 mm)	11-7/8" (302 mm)	48" (1219 mm)	40" (1016 mm)	32" (814 mm)	36" (914 mm)
12-3/16" (310 mm)	17-3/4" (450 mm)	9-1/8" (231 mm)	24" (610 mm)	16" (410 mm)	26" (661 mm)	30" (762 mm)
12-3/16" (310 mm)	17-3/4" (450 mm)	13-1/16" (332 mm)	24" (610 mm)	16" (410 mm)	36" (916 mm)	40" (1016 mm)
17-3/4" (450 mm)	12-3/16" (310 mm)	13-5/8" (346 mm)	30" (762 mm)	22" (560 mm)	26" (661 mm)	30" (762 mm)
12-3/16" (310 mm)	17-3/4" (450 mm)	15-1/16" (383 mm)	30" (762 mm)	22" (560 mm)	36" (916 mm)	40" (1016 mm)
17-3/4" (450 mm)	12-3/16" (310 mm)	14-1/8" (359 mm)	36" (914 mm)	28" (711 mm)	26" (661 mm)	30" (762 mm)
17-3/4" (450 mm)	12-3/16" (310 mm)	16-5/16" (415 mm)	36" (915 mm)	28" (711 mm)	36" (914 mm)	40" (1016 mm)
17-3/4" (450 mm)	12-3/16" (310 mm)	11-7/8" (302 mm)	48" (1219 mm)	40" (1016 mm)	32" (814 mm)	36" (914 mm)