

Features

- Tested and certified to California Title 24 standards and meets JA8 2016 requirements
- The Title 24 certified LED mirror has up to 60% more lumen output than the standard model. This increases the overall brightness of warm white light that illuminates your space and reflection
- The mirror's LED task lighting exceeds Title 24 requirements (< 10% minimum dimming level) with continuously dimmable brightness to 1%
- Includes mirror defogging
- Front and side diffuser, no visible LEDs
- Energy efficient LED lighting

Lighting Specs

Kelvin:	3000K
CRI:	90+
Lumens†:	3071
Lux†:	345
R9 Value:	50+
Foot-candles†:	32

†Measured at 18" from center of mirror, based on 36" x 40" size

Construction

- Anodized aluminum back frame
- Quality polished edge mirror
- Power cords installed for easy plugin installation
- Constructed for surface mounting
- Includes installation hardware


Dimensions

- 24" x 30" x 1-3/4" (610 mm x 762 mm x 45 mm)
- 24" x 40" x 1-3/4" (610 mm x 1016 mm x 45 mm)
- 30" x 40" x 1-3/4" (762 mm x 1016 mm x 45 mm)
- 36" x 40" x 1-3/4" (914 mm x 1016 mm x 45 mm)

Codes/Standards Applicable

Core Lighted Mirror is UL certified to:

- UL 962
- CSA-C22.2, No. 250.4




Savant Model Number

Product Description

SVTCM02430N03POK	Core Lighted Mirrors, 24" x 30", 3000K, Perimeter Light Pattern, Title 24 Compliant
SVTCM02440N03POK	Core Lighted Mirrors, 24" x 40", 3000K, Perimeter Light Pattern, Title 24 Compliant
SVTCM03040N03POK	Core Lighted Mirrors, 30" x 40", 3000K, Perimeter Light Pattern, Title 24 Compliant
SVTCM03640N03POK	Core Lighted Mirrors, 36" x 40", 3000K, Perimeter Light Pattern, Title 24 Compliant

Electrical System

- 120 VAC 60HZ wall outlet as shown in drawing



* See instructions 209-1277 for wiring and location

Dimensions					
A	B	C	D	E	F
13-3/4" (350 mm)	9-13/16" (250 mm)	15-3/16" (386 mm)	24" (610 mm)	30" (762 mm)	17-1/2" (445 mm)
12-3/16" (310 mm)	17-3/4" (450 mm)	16-7/16" (418 mm)	24" (610 mm)	40" (1016 mm)	17-1/2" (445 mm)
12-3/16" (310 mm)	17-3/4" (450 mm)	19" (483 mm)	30" (762 mm)	40" (1016 mm)	17-1/2" (445 mm)
12-3/16" (310 mm)	17-3/4" (450 mm)	19" (483 mm)	36" (914 mm)	40" (1016 mm)	17-1/2" (445 mm)