

## Features

- Chamfer Museum Frame: the angled design adds dimension for a unique look that pairs well with transitional and traditional environments
- Features a 3/8" gap between the edge of the mirror and the overall frame to create an even, uniformed illumination
- Match fixtures with metal frame finishes: Chrome, Polished Nickel, Matte Gold, Matte Black
- Tested and certified to California Title 24 standards and meets JA8 2016 requirements
- The Title 24 certified LED mirror has up to 60% more lumen output than the standard model. This increases the overall brightness of warm white light that illuminates your space and reflection
- The mirror's LED task lighting exceeds Title 24 requirements (< 10% minimum dimming level) with continuously dimmable brightness to 1%
- Includes mirror defogging
- Front and side diffuser, no visible LEDs
- Energy efficient LED lighting

## Lighting Specs

|                |           |
|----------------|-----------|
| Kelvin:        | 3000K     |
| CRI:           | 90+       |
| Lumenst:       | 2240-2910 |
| R9 Value:      | 50+       |
| Lux†:          | 331-342   |
| Foot-candles†: | 31-32     |

†Measured at 18" from center of mirror

## Construction

- Plated chrome and polished nickel finishes provide easy upkeep, exceptional durability, and a timeless look that complements any design
- Anodized matte gold and matte black finish options are easy to maintain and won't chip, peel, or fade – so you can enjoy their beauty for years to come
- Anodized aluminum back frame
- Quality polished edge mirror
- Power cords installed for easy plugin installation
- Constructed for surface mounting
- Includes installation hardware


## Dimensions

- 27" x 33" x 2-5/16" (686 mm x 838 mm x 58 mm)
- 27" x 43" x 2-5/16" (686 mm x 1092 mm x 58 mm)

## Codes/Standards Applicable

Framed Lighted Mirror is UL certified to:

- UL 962
- CSA-C22.2, No. 250.4




| Savant Model Number | Product Description                                                                                 |
|---------------------|-----------------------------------------------------------------------------------------------------|
| SVTFM02430NC3PCK    | Framed Lighted Mirrors, 27" x 33", Chamfer Museum Frame, Chrome, 3000K, Title 24 Compliant          |
| SVTFM02430NN3PCK    | Framed Lighted Mirrors, 27" x 33", Chamfer Museum Frame, Polished Nickel, 3000K, Title 24 Compliant |
| SVTFM02430NG3PCK    | Framed Lighted Mirrors, 27" x 33", Chamfer Museum Frame, Matte Gold, 3000K, Title 24 Compliant      |
| SVTFM02430NB3PCK    | Framed Lighted Mirrors, 27" x 33", Chamfer Museum Frame, Matte Black, 3000K, Title 24 Compliant     |

| Savant Model Number | Product Description                                                                                 |
|---------------------|-----------------------------------------------------------------------------------------------------|
| SVTFM02440NC3PCK    | Framed Lighted Mirrors, 27" x 43", Chamfer Museum Frame, Chrome, 3000K, Title 24 Compliant          |
| SVTFM02440NN3PCK    | Framed Lighted Mirrors, 27" x 43", Chamfer Museum Frame, Polished Nickel, 3000K, Title 24 Compliant |
| SVTFM02440NG3PCK    | Framed Lighted Mirrors, 27" x 43", Chamfer Museum Frame, Matte Gold, 3000K, Title 24 Compliant      |
| SVTFM02440NB3PCK    | Framed Lighted Mirrors, 27" x 43", Chamfer Museum Frame, Matte Black, 3000K, Title 24 Compliant     |

## Electrical System

- 120 VAC 60HZ wall outlet as shown in drawing



\*See instructions for wiring and location.

NOTE: Dimensions shown for both 24x30 mirror and 24x40 mirror.