

Sculpt Series Hanging Mirror
YM2033ANPFNZH Sculpt Hanging Arch Mirror Specification Sheet

FEATURES

- Arch shaped mirror with a hand finished metal frame
- Ceiling mounted for unique, high design installations
- Accommodates up to 11' high and lofted ceilings

MATERIALS & CONSTRUCTION


- Stainless steel frame
- Includes all required mounting hardware

OPTIONS

- Available in:
 - YM2033ANPFNZH83 - Matte Black
 - YM2033ANPFNZH84 - Polished Stainless Steel
 - YM2033ANPFNZH86 - Brass
- Coordinate with Magnification Mirrors
 - 5M0008FLUT76 - Freestanding Lit, Chrome
 - 5M0008FUUN70 - Freestanding, Satin Nickel
 - 5M0008FUUN76 - Freestanding, Chrome
 - 5M0008FUUN83 - Freestanding, Matte Black
 - 5M0008FUUN85 - Freestanding, Brushed Bronze

DIMENSIONS


- Width: 19-1/4" (489mm)
- Height: 33" (838mm)
- Depth: 1-7/8" (47mm)
- Install: 44-1/16" (1120mm) - 91-1/16" (2314mm)



MODEL NUMBER KEY

PRODUCT LINE	CATEGORY	WIDTH	HEIGHT	SHAPE	FINISH	OPTIONS
Y = Sculpt Series	M = Mirror	20	33	AN = Arch	PF = 1/2" Frame	NZ H = Ceiling Mounted

MORE INFORMATION



Scan the QR code to see the details found in the Sculpt Hanging Mirror installation instructions.

Use the camera app on your mobile device to look at this QR code. This will allow you to quickly access web pages and other relevant documents.

