

**Craft Series Linen Cabinet**  
**CSSM2080 Sinca Linen Cabinet Specification Sheet**

**FEATURES**

- Adjustable shelves
- Distinctive louvered door front details
- Adjustable leg levelers

**MATERIALS & CONSTRUCTION**


- Solid wood and veneer construction
- Tapered legs with stretcher support for increased strength
- Full plywood back panel, no cutout
- Adjustable Blum 92° soft-close hinges

**OPTIONS**

- Available in:
  - CSSN2080217 - White Oak
  - CSSN2080218 - Walnut

**DIMENSIONS**


- Width: 20" [508mm]
- Height: 80" [2032mm]
- Depth: 16" [406mm]



**MODEL NUMBER KEY**

PRODUCT LINE	CATEGORY	COLLECTION	SIZE	FINISH OPTIONS
C = Craft Series	S = Storage	SN = Sinca	2080	(See above)

**MORE INFORMATION**



Scan the QR code to see the details found in the Craft Vanity installation instructions.

Use the camera app on your mobile device to look at this QR code. This will allow you to quickly access web pages and other relevant documents.

