

**Features**

- Three-way mitered joinery on vanity frame
- Mitered thin frame drawer detail
- Top drawer is a plumbing drawer
- Bottom drawer is a plumbing drawer
- Open shelf storage
- Removable glass drawer dividers included

**Materials & Construction**


- Solid wood and veneer construction
- Full plywood back panel, no cutout
- Dovetailed drawers
- Pre-installed solid stainless steel hardware
- Blum undermount full extension slow close slides
- Durable, moisture resistant polyurethane finish
- Adjustable leveling feet

**Options**

- Available in:  
 CVSK3620469, Rustic Oak paired with Brushed Pewter
- Coordinating mineral cast sink with infinity drain, TA36MCO\_\_\_-8CS8
- Coordinating mirrors available
- Coordinating linen cabinet available

**Dimensions**



Width: 35-5/8"  
 Height: 28-1/8"  
 Depth: 22-3/4"



**Model Number Key**

PRODUCT LINE	CATEGORY	COLLECTION	WIDTH	FINISH OPTIONS	OPTIONS
C = Craft Series	V = Vanity	SK = Skaarsgard	36"	(See above)	(See above)

Skaarsgard 36" Vanity CVSK36



**Features**


- Mineral cast integrated sink and top
- Removable infinity drain cover

**Options**

- Available finish:  
102, Matte White
- Pairs with Craft Series Bodo & Skaarsgard 36" vanities

**Dimensions**

Width: 36"  
 Height: 6"  
 Depth: 23"



**Model Number Key**

CATEGORY	DEPTH	WIDTH	LAV TYPE	OVERFLOW	COLORS	DASH	FAUCET HOLES	OPTIONS
T = Top	A = 23" Depth Fabricated Top	36"	M = Machined/ Molded	C = Center Mounted	(See above)	-	8 = 3 Holes Drilled (Centered on Lav Location)	(See above)

36" Integrated Basin TA36MCOXXX-8CS8

