

Statuesque Wall Mirror
CM8644RPFPN3JU Lighted Perimeter Mirror Specification Sheet

FEATURES

- Dimmable LED task lighting to 1%
- Compatible with most Triac/Phase-cut dimmers
- Energy efficient LED lighting (measurements may vary):

Kelvin	3000K
CRI	90+
Lumens*	3400
R9 Value	50+
Wattage	110 W

* Estimated values

MATERIALS & CONSTRUCTION

- Anodized aluminum back frame
- Quality polished edge mirror
- Power cord installed for easy plug-in installation
- Constructed for surface mounting
- Includes installation hardware

CODES/STANDARDS APPLICABLE

Vitality Mirror is UL certified to:

- UL 962
- CSA-C22.2, No. 12-82

DIMENSIONS

- Width: 86" (2184mm)
- Height: 44" (1118mm)
- Depth: 1-3/4" (44mm)



MODEL NUMBER KEY

PRODUCT LINE	WIDTH	HEIGHT	SHAPE / PATTERN	FINISH	COLOR TEMP		
CM = Statuesque Mirror	86	44	RP = Rectangular Perimeter	FP = Flat Polished	N	3 = 3000K	J U

