


**Features**

- Stunning glass tops feature rectangular integrated sink, without overflow.
- Includes Drain spacer gasket kit

**Dimensions**

Width: 25" (635 mm)  
 Depth: 19" (483 mm)  
 Thickness: 19/32" (15 mm)  
 Weight: 30 lbs (13.6 kg)



**Options**

- Faucet Hole Patterns available:
  - Single Hole
  - 8" Widespread Three Hole
- Other widths available -
  - 31" (787 mm)
  - 37" (940 mm)
- Other depths available -
  - 22" (559 mm)

**Model Number Key**

T C 25 U C N 21 - \_

Category	T = Top
Series	C = 19" (483 mm)
Width	25" (635 mm)
Sink Type	U = Undercounter Sink
Sink Location	C = Center
Overflow	N = No overflow
Colors	21 = White
Faucet Hole Drilling	1 = Single-Hole (Centered on Sink Location) 8 = 3-Hole (Centered on Sink Location)

## Dimensions

