

Features

- Tested and certified to California Title 24 standards and JA8 2016 requirements
- Includes mirror defogging
- Dimmable LED task lighting to 1%
- Compatible with most Triac/Phase-cut dimmers
- Energy efficient LED lighting: (measurements may vary)

| | |
|------------------------|------|
| Kelvin | 2700 |
| CRI | 90+ |
| Lumens (Approx) | 3071 |
| R9 Value | 50+ |
| Lux* (Approx) | 345 |
| Foot-candles* (Approx) | 32 |

* Measured at 18" from center of the mirror

Construction

- Anodized aluminum back frame
- Quality polished edge mirror
- Power cords installed for easy plugin installation
- Constructed for surface mounting
- Includes installation hardware

Codes/Standards Applicable

Vitality Mirror is UL certified to:


- UL 962
- CSA-C22.2, No. 12-82

Dimensions

Height: 40" (1016 mm)
 Width: 36" (914 mm)
 Depth: 1-3/4" (45 mm)
 Net Weight: 23 - 39 lbs


Electrical System

- 120 Vac 60Hz wall outlet location as shown in drawing



Model Number Key

| Vitality | Mirror | Width | Height | Shape | Light Pattern | Edge Type | Defogger | Color Temp | Options |
|----------|--------|-------|--------|---------------|---------------|---------------------|--------------|------------|------------------------------|
| Y | M | 36 | 40 | R = Rectangle | P = Perimeter | FP = Flat, Polished | D = Defogger | 3 = 2700K | K = Title 24 Compliant Model |



* See instructions 209-1277 for wiring and location