


Options

•Available in:

- AS19290, Carrara marble with Drifted Matte Brown & Iron Black hardware
- AS19291, Carrara marble with Weathered Oak Drift & Antique Bronze hardware
- AS19292, Calacatta marble with Drifted Matte Brown & Iron Black hardware
- AS19293, Calacatta marble with Weathered Oak Drift & Antique Bronze hardware



Features

- Distinctive mitered raised panel doors
- Matching raised panel sides
- Richly textured oak finish
- Decorative metal leg detail
- Adjustable storage shelves

Materials & Construction


- Solid wood and veneer construction
- Full plywood back panel, no cutout
- Stainless steel ring pulls
- Blum slow close hinges
- Durable, moisture resistant polyurethane finish
- Adjustable leveling feet

Options

- Available in:
 CVWI7221368, Drifted Matte Brown paired with Iron Black
 CVWI7221088, Weathered Oak Drift paired with Antique Bronze
- Coordinating Ann Sacks Top
- Coordinating mirrors available



Dimensions

Width: 71"
 Height: 32-7/8"
 Depth: 22-1/2"



Model Number Key

PRODUCT LINE	CATEGORY	COLLECTION	WIDTH	FINISH OPTIONS	OPTIONS
C = Craft Series	V = Vanity	WI = Willowmere	72"	(See above)	(See above)



Features

- Stone top is fabricated with pre-drilled knock-outs, accommodating a deck mounted or a wall mounted faucet
- The Willowmere stone top is fabricated for the Kallista Perfect Centric Rectangle Basin
- Stone tops are honed, we recommend sealing prior to use with a penetrating sealer
- Periodic cleaning and resealing of the stone top is recommended using products formulated for natural stone

Materials & Construction

- Stone tops are fabricated from marble originating in Italy and Portugal

Options

- Available in:
 - AS19023, Carrara Top
 - AS19024, Calacatta Top

Dimensions

Width: 72"

Height: 1"

Depth: 23"

