



Record your model number: _____

1413577-W2

⚠ WARNING: Risk of scalding. High water temperature can cause severe burns. Verify that the delivered water is set at or below 120°F (49°C). Refer to the temperature adjustment steps in the trim installation instructions.

Follow all local plumbing and building codes.

Your product may appear different than the one illustrated. The installation procedure is the same.

- 2A. Cut the foam guard flush with the finished wall.
- 5A. Press the stems to pop to the extended position.
- 6A. With the stems in the extended position, cut flush with the white shrouds.
- 7A. Remove and discard the shrouds.
- 9A. Click the plates in place from left to right, according to outlet function.
- 10A. Verify "UP" is at the top.
- 11A. Push firmly in place. Secure using the provided 2.5 mm hex wrench.
- 12A. Push the clip firmly into place.

Maintenance

- 13A. **Maximum Temperature Adjustment:** Turn the handle to the 37°C position.
- 13B. Rotate the stem and test the water temperature. Set between 36°C and 38°C.
- 13C. Reinstall the stem extension and handle, aligned with the 37°C position.
- 14A. **Clean the Filters:** Remove the trim parts.
- 14B. Remove the cartridges. Note the hot and cold positions for reinstallation.
- 14C. Rinse debris from the filters, then reinstall all parts.

Need help? Contact our Customer Service.

- Email: technicalsupport@kohler.co.uk
- 0800 001 4466

This product is covered under the **KOHLER® Taps and Shower Valves Five-Year Limited Guarantee**. For a hardcopy of guarantee terms, contact Customer Service.



