


10215T-4 单孔面盆龙头
10217T-4 高把单孔面盆龙头



**订购时请说明颜色编号

**Color code must be specified when ordering

10215T-4 单孔面盆龙头
10217T-4 高把单孔面盆龙头

安装之前

所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。

说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。

注意事项:

1. 一定要先彻底冲洗供水管以清除管道中的杂质。
2. 检查供水管有无损坏和漏水。如需要，进行替换和维修。
3. 遵守当地管路安装条例。
4. 尽可能在安装面盆之前安装水龙头。

BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

Please leave these instructions for the consumer. They contain important information.

NOTES:

1. Flush the water supply pipes thoroughly to remove debris.
2. Inspect the supply tubing for damage and leakage. Replace and maintain as necessary.
3. Observe local plumbing codes.
4. If possible, install this faucet before installing the lavatory.

使用说明


将手柄轻轻提起，向左转为热水，向右转为冷水。

HANDLE OPERATION

Lift the handle gently. Turn left for hot water, right for cold water.

安装尺寸

ROUGH-IN DIMENSIONS



安装步骤


如何安装水龙头

将固定螺栓(1)装到龙头上，把供水软管(2)插入面盆安装孔中。

对于10215T-4，将托架(3)和垫片(4)套在固定螺栓上。调整水龙头的位置，锁紧螺母(5)以固定水龙头。

对于10217T-4，将托架(6)套在固定螺栓上。调整水龙头的位置，锁紧螺母(7)以固定水龙头。

把软管接到水源，面对水龙头时，左边为热水，右边为冷水。



INSTALLATION

How To Install The Faucet

Install mounting studs(1) into the faucet base. Insert the flexible hoses(2) into the mounting hole of the lavatory.

For 10215T-4, place the brackets(3) and washers(4) onto the mounting studs. Position the faucet. Tighten the nuts(5) to secure the faucet.


For 10217T-4, place the brackets(6) onto the mounting studs. Position the faucet. Tighten the nuts(7) to secure the faucet.

Attach the hoses to water supplies. When facing front of faucet, the left hose is hot water, the right hose is cold water.

如何安装排水器

仅对于10215T-4

将盘片(8)从排水本体(9)上取下，在排水器盘片底部套上垫片(10)，用密封胶带(生料带)在排水器尾管(11)缠几圈，装入排水本体。把排水本体从下方插入洗面盆，排水杆口(12)朝后方，把排水器盘片旋入排水本体中，从下方用手拧紧锁紧螺母(13)。



How To Install The Drain Only For 10215T-4

Remove the flange(8) from drain body(9). Slide the washer(10) onto the underside of the drain flange. Apply thread tape to tailpiece(11). Install to drain body. Insert drain body into underside of lavatory with drain lever hole(12) facing to the back of lavatory and thread flange onto drain body until hand tight. Tighten the locknut(13) by hand from the underside of the fixture.


Place stopper(14) into drain body aligning the flat side of stopper hole(15) with the drain lever hole.

NOTE: If needed, apply a ring of plumbers putty or other sealants around the underside of the drain flange(8), instead of using rubber washer(10).

Place the rubber washer(16) into the drain lever hole. Put another plastic washer(17) and retaining nut(18) into the long end of ball lever rod(19). Insert the ball lever assembly(20) into the drain lever hole and through the stopper hole(15), and tighten the retaining nut.

Be sure that the ball lever points to the back of the lavatory. Tighten the locknut(13) onto the drain body. Remove any excess putty.


NOTE: Do not reposition the drain after the locknut is tightened, or you may break the putty seal.



确定球动杆指向洗面盆后方，再次拧紧排水本体的锁紧螺母(13)，去除多余油灰。

注意：在锁紧螺母拧紧后，不可调整排水本体的位置，否则会破坏油灰密封或密封剂密封。


把手捻螺丝(21)装到联杆(22)上。用“V”形夹(23)将联杆连接到球动杆组件上，将提拉杆(24)插入水龙头及联杆的孔中，调整提拉杆的位置(将球动杆下推至排水组件全开位置，调整提拉杆使提拉杆头与台面高度控制在80~85毫米)。



拧紧手捻螺丝。

仅对于10217T-4

把锁紧螺母(25)、塑料垫片(26)、橡胶垫圈(27)和尾管(28)从排水本体上取下。在尾管螺纹处须缠绕足以密封的密封胶带或涂合适的密封胶，装回排水本体。把排水本体从面盆上部孔插入。再依次将橡胶垫圈(小面朝上)、塑料垫片和锁紧螺母从排水本体底部装入。锁紧螺母。




注意：如果需要，可直接在排水器盘片(29)底面沿周围涂一圈密封油灰或其他密封剂，而不使用橡胶垫片(30)。

注意：在锁紧螺母拧紧后，不可调整排水本体的位置，否则会破坏油灰密封或密封剂密封。

安装结果检查

检查并确保所有衔接处都已拧紧，确保手柄在关的位置。



打开主要供水源和排水系统，检查并修理有漏水的接口。

将起泡器组件(31)拆下，打开水龙头的冷热水，让水流约一分钟以清除杂质，检查渗漏。冲洗起泡器组件，关闭水龙头，重新装回起泡器组件。

清洗说明

适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净的软布彻底擦干整个表面，许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。

有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。

Assemble thumb screw(21) to link(22), and link onto ball lever rod with “V”-clip(23). Slide lift rod(24) through the hole in faucet and into the hole in link. Position te lift rod (Push the ball lever down into the open position, and adjust the lever to make sure the height between lift rod and table is controlled within the range of 80~85mm).

Tighten thumb screw.position.

Only For 10217T-4

Remove the locknut(25), plastic washer(26), rubber gasket(27) and tailpiece(28) from the drain body. Supply enough tape or sealant to tailpiece thread. Reinstall the tailpiece. Insert the drain body into the lavatory. Put the rubber gasket (Tapered side up), plastic washer and locknut back to the drain body in turn. Tighten the clocknut.

NOTE: If needed, apply a ring of plumbers putty or other sealants around the underside of the drain flange(29), instead of using rubber washer(30).

NOTE: Do not reposition the drain after the locknut is tightened, or you may break the putty or sealant seal.

INSTALLATION CHECKOUT

Ensure that all coupling nuts are tight. Ensure that the lever handle is in the off position.

Turn on the main water supply and drain, and check for leaks. Repair as needed.

Remove the aerator assembly(31). Run hot and cold water through faucet for about one minute to remove any debris. Check for leaks. Repair as needed. Remove any debris from the aerator assembly. Shut off the faucet. Reinstall the aerator assembly.

CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.