

Product

- Taut Pull Down Kitchen Spray

Kohler Code

21367T-4E-CP

**Features**

- Two-function spray head with spray & aerated flow function
- Ball joint on spray head
- 360° swivel gooseneck spout
- Easy clean nozzle
- Ceramic disc valve
- Quiet nylon retractable hose
- Dual check valve complying to AS/NZS 3500.1
- Suitable for mains pressure
- KOHLER finishes resist tarnishing and corrosion




WELS RATING
(5 Star 6 Litres / min)

Related Products


- Taut tapware

Technical Details

Front View



Side View



G½" is equal to BSP½" female

Installation Notes:

- G1/2" female inlets.
- Optimum working pressure 300-500 kPa.
- Where normal working pressure exceeds the maximum, pressure limiting valves should be installed.
- Maximum working temperature 60°C.
- Maximum bench thickness is 45mm.
- Inline filters should be used to protect tapware from debris that may be present within the plumbing.