

Features

- Digitally controlled thermostatic mixing valve.
- Antiscald protection.
- Built-in temperature and flow control.
- Up to 12 gpm (45.4 lpm) flow rate at 45 psi (3.1 bar) with maximum flow of 9.5 gpm (36 lpm) from one outlet.
- Two independently controllable 15 mm plastic outlets for push-fit connection.
- 15 mm plastic inlets for push-fit connection.

Material

- Reinforced engineering-grade thermoplastic body.

Installation

- Install valve approximately 32' (9754 mm) away from the digital control (cable supplied with control).
- Prewired with three-pin plug for connection to 230v RCD electrical outlet.
- Requires Anthem digital control (sold separately).

Required Products/Accessories


For wall-mount installation
K-28214 Digital control

Optional Products/Accessories

K-28213 Remote on/off button for digital thermostatic valve

Included Components

Additional Components:
Filter Screens (Qty 2)
Jumper
Mounting Hardware
Power Supply Unit




Codes/Standards

None Applicable

KOHLER® Taps and Shower Valves Five-Year Limited Guarantee

See website for detailed warranty information.

The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license. Other trademarks and trade names are those of their respective owners.



Required Electrical Service

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Thermostatic valve: 120/240 V, 1 A, 50/60 Hz

Technical Information

All product dimensions are nominal.

Power source: Plug - AC, included

Shower Valve:

| | |
|------------------------------------|-------------------------|
| Flow Rate (Max) @ 45 psi | 12 gal/min (45.4 l/min) |
| Manufacturer's minimum rated flow: | 0.9 gal/min (3.4 l/min) |
| Pressure: | 45 psi (3.1 bar) |
| Maximum (Static) Pressure: | 125 psi (8.6 bar) |
| Minimum (Operating) Pressure: | 15 psi (1 bar) |

Valve body: Plastic

Drain included: No

Electrical component Thermostatic valve: 120/240 V, 1 A,
rating: 50/60 Hz

Cable length: Data, 32 ft (9.8 m)

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com.

4-28-2022 10:10 - GB