

HIGHLINE_®

Features

- Vitreous china
- Elongated bowl
- Equipped with Sloan FLUSHMATE® Sloan® Valve Company
- Polished chrome trip lever
- Less seat and supply
- 12" (305 mm) rough-in
- 1.6 gpf (6.0 lpf)
- 2-1/4" (57 mm) glazed trapway
- 12" (305 mm) x 10" (254 mm) water area
- 30-1/8" (765 mm) x 21-1/4" (540 mm) x 31-1/4" (794 mm)

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ADA
- ICC/ANSI A117.1
- CSA B651
- OBC
- ASME A112.19.2/CSA B45.1

PRESSURE-LITE® TOILET **K-3493**

OBC ADA CSA B651



Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Accessories

- 0: White
- · CP: Polished Chrome
- PB: Vibrant_® Polished Brass
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Trip Lever	Colors/Finishes	
K-3493	Pressure-Lite toilet	left-hand	□ 0	□ Other
K-3493-RA	Pressure-Lite toilet	right-hand	□ 0	☐ Other
K-3493-T	Pressure-Lite toilet with tank cover locks	left-hand	□ 0	☐ Other
K-3493-TR	Pressure-Lite toilet with tank cover locks	right-hand	□ 0	☐ Other

Recommended Accessories					
K-4650	Lustra™ elongated open-front toilet seat – for Accessibility compliance	□ 0		☐ Other	
K-4664	Brevia™ seat with cover	□ 0		☐ Other	
K-7637	Angle supply with stop	□ CP	□ PB	☐ Other	

Product Specification

The elongated bowl toilet shall be made of vitreous china. Toilet shall be 30-1/8'' (765 mm) in length, 21-1/4'' (540 mm) in width, and 31-1/4'' (794 mm) in height with a 12'' (305 mm) x 10'' (254 mm) water area. The toilet shall be 12'' (305 mm) rough-in. The toilet shall be equipped with Sloan Flushmate - Sloan Valve Company. Toilet shall be 1.6 gpf (6 lpf). Toilet shall include polished chrome trip lever. Toilet shall be less seat and supply. Toilet shall be Kohler Model K-3493-

HIGHLINE_®

Technical Information

Fixture:			
Configuration	two-piece, elongated		
Water per flush	1.6 gallons (6 L)		
Passageway	2-1/4" (57 mm)		
Water area	12" (305 mm) x 10" (254 mm)		
Water depth from rim	5-3/4" (146 mm)		
Seat post hole centers	5-1/2" (140 mm)		
Minimum static pressure required	20 psi (137.9 kPa)		
Maximum static pressure	80 psi (551.6 kPa)		

Included Components*:				
Bowl	K-4304			
Tank	K-4645			
Tank cover	1036375			
Trip lever	K-9481			
Tank accessory pack	73062			
Bolt cap accessory pack	52048			
*Equipped with Sloan Flushmate™ – Sloan Valve Company				

Installation Notes

Install this product according to the installation guide.

For back-to-back toilet installations: Use only a 45° double wye fitting.

Will comply with the American Disabilities Act (ADA) when installed per the requirements of the Accessibility Guidelines, Section 604 Water Closets, of the Act. The Model Plumbing Codes require the installation of elongated open-front toilet seats in public bathrooms.

Will comply with **CSA B651** when installed per Clause 4.3.6 of the standard.

Will comply with OBC when installed per Clause 3.8.3.8 and 3.8.3.9.

