



## SPECIFICATIONS

**Bowl K-3385-CA with:**

Tank cover .....	K-4604
Float valve .....	30730
Flush valve .....	81730
Bolt caps (pr.) .....	52048
Trip lever .....	K-9415
1/2" supply .....	56281
Seat .....	K-4675

**When specified:**

Floor bolts (pr.) .....	21401
-------------------------	-------

## NOTES

For most satisfactory operation a minimum running pressure of 25 p.s.i. is required at the toilet supply inlet.  
 Seat post holes on 5-1/2" centers.  
 Water depth from rim is 6-3/4".  
 2-1/4" passageway.  
 Fixture dimensions are nominal and conform to tolerances by ANSI standard A112.19.2.