


#### Features

- KOHLER cast iron
- Acid-resistant enamel finish
- 2-hole
- 8" (20.3 cm) high back
- Installation hardware included
- 24" (61 cm) x 18" (45.7 cm)

#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.1M
- IAPMO/UPC
- CSA B45



#### Colors/Finishes

- 0: White

#### Accessories:

- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes

#### Specified Model

Model	Description	Colors/Finishes	
K-5980	Utility sink	<input type="checkbox"/> 0	
<b>Recommended Accessories</b>			
K-9000	P-Trap	<input type="checkbox"/> CP	
<b>Optional Accessories</b>			
K-8801	Duostrainer® sink strainer	<input type="checkbox"/> CP	<input type="checkbox"/> Other_____

#### Product Specification

The utility sink shall be made of cast iron with acid-resistant enamel finish. Sink shall be 2-hole. Sink with 8" (20.3 cm) high back shall be 24" (61 cm) in length and 18" (45.7 cm) in width. Sink shall include installation hardware. Sink shall be Kohler Model K-5980-0.

# SUTTON™


## Technical Information

Fixture*:	
Basin area	19" (48.3 cm) x 14" (35.6 cm)
Water depth	6" (15.2 cm)
Drain hole	3-5/8" (9.2 cm) D.
Faucet holes	1-1/2" (3.8 cm) D.
* Approximate measurements for comparison only.	

Included component:	
Hanger	64503

## Installation Notes

Install this product according to the installation guide.



## Product Diagram