KOHLER®

Roughing-In

K-3598
STRELA™
DUAL FLUSH TOILET

Product Information

Applicable product:	
Dual Flush toilet	K-3598

Fixture:	
Configuration	two-piece, elongated
Water per flush	1.6 gpf (6 lpf) or 0.9 gpf (3.4 lpf)
Passageway	2″ (5.1 cm)
Water area	4-1/4″ (10.8 cm) x 6-5/16″ (16 cm)
Water depth from rim	8-1/8″ (20.6 cm)
Seat post hole centers	5-1/2″ (14 cm)

Included components:	
Bowl	K-4379
Tank	K-4742
Tank cover	1080568
Push buttons	1072961

Installation Notes

IMPORTANT! The rough-in must be 12″ (30.5 cm) from the finished wall or baseboard. Install or relocate the supply and outlet as necessary to conform to rough-in dimensions.

NOTE: If a baseboard interferes with the toilet, it must be cut or removed to allow space for the toilet.

If this toilet is installed to new construction, install a new supply stop following the dimensions in the diagram.

In installations with the supply stop installed, the existing supply stop may need to be relocated if it is less than 6″ (15.2 cm) from the centerline of the toilet. Dry fit the toilet to confirm if the supply stop needs to be relocated.

Install this product according to the installation guide.

Fixture conforms to ASME Standard A112.19.2/CSA B45.1. All dimensions are nominal.

