KOHLER®

MEMOIRS®


THE COMPLETE SOLUTION® TOILET
K-10494

ADA | **CSA B651** | **OBC**

WaterSense Meets EPA Criteria. Certified by IAPMO R&T

Features

- *Vitreous china*
- *Elongated bowl*
- *Comfort Height®*
- *AquaPiston® flushing system*
- *Includes seat, cover, wax ring, left-hand polished chrome trip lever, and floor hardware*
- *Quiet-Close™ Quick-Release™ toilet seat and cover*
- *Less supply*
- *12″ (305 mm) rough-in*
- *1.28 gpf (4.8 lpf)*
- *2-1/8″ (54 mm) glazed trapway*
- *11-3/4″ (298 mm) x 9-1/2″ (241 mm) water area*
- *30-3/8″ (772 mm) x 18-7/8″ (479 mm) x 31-1/16″ (789 mm)*



Codes/Standards Applicable

Specified model meets or exceeds the following:

- *ADA*
- *ICC/ANSI A117.1*
- *CSA B651*
- *OBC*
- *ASME A112.19.2/CSA B45.1*
- *Energy Policy Act of 1992*

Colors/Finishes

- 0: White

Accessories

- 0: White
- CP: Polished Chrome
- PB: Vibrant® Polished Brass
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Trip Lever	Colors/Finishes
K-10494	The Complete Solution toilet	left-hand	❑ 0

Recommended Accessories					
K-4650	Lustra™ elongated open-front toilet seat – for Accessibility compliance	❑ 0			❑ Other_____
K-7637	Angle supply with stop – 3/8″ NPT		❑ CP	❑ PB	❑ Other_____

Product Specification

The elongated bowl toilet shall be made of vitreous china. Toilet shall be 30-3/8″ (772 mm) in length, 18-7/8″ (479 mm) in width, and 31-1/16″ (789 mm) in height with an 11-3/4″ (298 mm) by 9-1/2″ (241 mm) water area. Toilet shall be 1.28 gpf (4.8 lpf) with AquaPiston flushing system. Toilet shall be Comfort Height and less supply. Toilet shall be 12” (305 mm) rough-in with a 2-1/8″ (54 mm) glazed trapway. Toilet shall include Quiet-Close Quick-Release toilet seat and cover. Toilet shall include seat, cover, wax ring, left-hand polished chrome trip lever, and floor hardware. Elongated bowl toilet shall be Kohler Model K-10494-_____.

USA/Canada: 1-800-4KOHLER
(1-800-456-4537)
www.kohler.com

MEMOIRS®

Technical Information

Fixture:	
Configuration	two-piece, elongated
Water per flush	1.28 gpf (4.8 lpf)
Passageway	2-1/8″ (54 mm)
Water area	11-3/4″ (298 mm) x 9-1/2″ (241 mm)
Water depth from rim	6-1/8″ (156 mm)
Seat post hole centers	5-1/2″ (140 mm)

Included components:	
Bowl	K-4380
Tank	K-4434
Tank cover	1052862
Trip lever, left-hand	K-9167
Toilet seat	K-4733
Bolt cap accessory pack	1013092
Wax ring and hardware installation kit	1023457

Installation Notes

Install this product according to the installation guide.

For back-to-back toilet installations: Use only a 45° double wye fitting.


Will comply with the Americans with Disabilities Act **(ADA)** when installed per the requirements of the 2010 ADA Standards for Accessible Design, Section 604 Water Closets, of the Act. The Model Plumbing Codes require the installation of elongated open-front toilet seats in public bathrooms.

The model is acceptable for left-hand Accessible compartment installations only.

Will comply with **CSA B651** when installed per Clause 4.3.6 of the standard.

Will comply with **OBC** when installed per Clause 3.8.3.8 and 3.8.3.9.

Fixture conforms to ASME Standard A112.19.2/CSA B45.1. All dimensions are nominal.



Product Diagram

THE BOLD LOOK OF KOHLER®