


Features

- Vitreous china
- Elongated bowl
- Comfort Height®
- AquaPiston® flushing system
- Includes seat, cover, wax ring, left-hand polished chrome trip lever, and floor hardware
- 12" (305 mm) rough-in
- 1.28 gpf (4.8 lpf)
- 2-1/8" (54 mm) glazed trapway
- Less supply
- 11-1/2" (292 mm) x 8-1/2" (216 mm) water area
- 29" (737 mm) x 17-7/8" (454 mm) x 30" (762 mm)

THE COMPLETE SOLUTION® TOILET K-10495



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ADA
- ASME A112.19.2/CSA B45.1
- ICC/ANSI A117.1
- EPA WaterSense®

Colors/Finishes

- 0: White

Accessories

- 0: White
- CP: Polished Chrome
- PB: Vibrant® Polished Brass
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Trip Lever	Colors/Finishes
K-10495	The Complete Solution toilet	left-hand	☐ 0

Recommended Accessories					
K-4650	Lustra™ elongated open-front toilet seat – for ADA compliance	☐ 0			☐ Other_____
K-7637	Angle supply with stop – 3/8" NPT		☐ CP	☐ PB	☐ Other_____

Product Specification

The elongated bowl toilet shall be made of vitreous china. Toilet shall be 29" (737 mm) in length, 17-7/8" (454 mm) in width, and 30" (762 mm) in height with an 11-1/2" (292 mm) by 8-1/2" (216 mm) water area. Toilet shall be 1.28 gpf (4.8 lpf) with AquaPiston flushing system. Toilet shall feature Comfort Height and 2-1/8" (54 mm) glazed trapway. Toilet shall include seat, cover, wax ring, left-hand polished chrome trip lever, and floor hardware. Toilet shall be 12" (305 mm) rough-in. Toilet shall be less supply. Elongated bowl toilet shall be Kohler Model K-10495-_____.

ARCHER™

Optional Accessories

K-11069	Left-hand trip lever (non-CP finish)	☐ PB	☐ Other_____
---------	--------------------------------------	-----------------------------	-------------------------------------

Technical Information

Fixture:	
Configuration	two-piece, elongated
Flush rate	1.28 gpf (4.8 lpf)
Passageway	2-1/8" (54 mm)
Water area	11-1/2" (292 mm) x 8-1/2" (216 mm)
Water depth from rim	6-1/4" (159 mm)
Seat post hole centers	5-1/2" (140 mm)

Included components:	
Bowl	K-4356
Tank	K-4431
Tank cover	1046467
Trip lever, left-hand	1067186
Toilet seat	K-4774
Tank accessory pack	1016548

Bolt cap accessory pack	1013092
Wax ring and hardware installation kit	1023457


Installation Notes

Install this product according to the installation guide.

For back-to-back toilet installations: Use only a 45° double wye fitting.

Will comply with the Americans with Disabilities Act (ADA) when installed per the requirements of the 2010 ADA Standards for Accessible Design, Section 604 Water Closets, of the Act. The Model Plumbing Codes require the installation of elongated open-front toilet seats in public bathrooms.

The model is acceptable for left-hand Accessible compartment installations only.



Product Diagram