

Ceramic/Impressions®

Vanity Top Bathroom Sink K-2791-1

Features

- Integrated sink and vanity top.
- Single faucet hole.
- Oval basin.
- Overflow drain.
- Raised outer edge helps contain water and prevents items from rolling off the vanity top.
- Dimensional colors.
- Coordinates with the industry-standard 24-inch vanities in the KOHLER® Tailored vanity collection.

Material

Vitreous china.

Installation

• Vanity top.



Codes/Standards

ASME A112.19.2/CSA B45.1

KOHLER[®] One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.


Color	Code	Description
	G81	White Impressions
	G82	Dune Impressions
	G83	Biscuit Impressions
	G85	Sandbar Impressions
	G86	Cashmere Impressions
	G88	Thunder Grey Impressions





Ceramic/Impressions®

Vanity Top Bathroom Sink K-2791-1



Technical Information

All product dimensions are nominal.			
Single			
ТВ			
Length: 17" (432 mm) Width: 13-3/8" (340 mm) Bowl depth: 5-1/2" (140 mm) With overflow: Yes Water depth: 4" (102 mm)			
1			
1-3/8" (35 mm)			
1-3/4" (44 mm)			

Notes

Install this product according to the installation instructions.

This sink is designed to be installed as an integrated vanity top to a KOHLER or standard vanity.

