



## Brockway™

Utility Sink  
K-3202

### Features

- Kohler plumbing products mean beautiful form as much as reliable function
- Drilled for two K-8892 Cannock™ faucets and one K-8880 soap dish
- Constructed KOHLER® Cast Iron
- Acid resistant enamel finish
- The bottom of the sink is an unpainted, ground-coat surface.

### Recommended Accessories

K-8820 Sink Drain and Strainer  
K-8880 Soap Dish  
K-8892 double lever handle wash sink faucet  
K-8801 Sink Strainer  
K-8799 Sink Strainer

### Optional Accessories

K-3264-PP Bathroom Sink Pedestal  
K-3265-P Bathroom Sink Pedestal

### Components

Additional included component/s: Hangers.



### Codes/Standards

ASME A112.19.1/CSA B45.2


### KOHLER® Enameled Cast Iron Kitchen Sink Lifetime Limited Warranty


See website for detailed warranty information.

### Available Color/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	0	White
--	---	-------



#### Technical Information

All product dimensions are nominal.

Bowl configuration: Single

Installation: Top-mount

Bowl area (Only): Length: 44" (1118 mm)  
Width: 14" (356 mm)  
Water depth: 7" (178 mm)

Number of deck holes: 4

Faucet hole(s): 1-1/2" (38 mm)

Soap/Lotion hole: 5/16" (8 mm)

Drain hole: 2-1/8" (54 mm)

#### Notes

Install this product according to the installation instructions.