


mm	A	B	C	D	
E62461	900	760	25	14	9
E62484	1000	700	25	12	9
E62446	1000	760	25	12	9
E62447	1000	800	25	12	9
E62448	1100	800	25	12	11
E62485	1200	700	25	9	11
E62449	1200	760	25	9	11
E62450	1200	800	25	9	11
E62451	1200	900	25	9	11
E62486	1400	700	25	5	13
E62452	1400	760	25	5	13
E62453	1400	800	25	5	13
E62481	1400	900	25	4	13
E62487	1500	700	24	3	13
E62454	1500	760	24	3	13
E62455	1600	700	24	4	13
E62456	1600	760	24	4	13
E62482	1600	900	24	4	13
E62457	1700	700	24	4	13
E62458	1700	760	24	4	13
E62483	1700	900	24	4	13