



Mm	A	B
E62624	900 ⁰ ₋₅	900 ⁰ ₋₅
E62625	1000 ⁰ ₋₅	800 ⁰ ₋₅
E62626	1000 ⁰ ₋₅	900 ⁰ ₋₅
E62627	1200 ⁰ ₋₅	800 ⁰ ₋₅
E62628	1200 ⁰ ₋₅	900 ⁰ ₋₅