



Mm	A	B	C (face supérieure)	D (face inférieure)	E (face supérieure)	F (face inférieure)	Y
E66510	800	800	678	688	143	159	18
E66511	900	900	778	790	143	159	16
E66517	1000	700	578	591	143	159	11
E66512	1000	800	678	688	143	159	18
E66550	1000	900	778	790	143	159	16
E66518	1200	700	578	591	143	159	11
E66513	1200	800	678	688	143	159	18
E66514	1200	900	778	790	143	159	16
E66551	1200	1000	778	790	143	159	16
E66552	1400	700	778	790	143	159	16
E66515	1400	800	578	591	143	159	18
E66516	1400	900	778	790	143	159	11
E66553	1400	1000	778	790	143	159	16
E66519	1500	800	678	688	143	159	18
E66520	1600	800	678	688	143	159	18
E66521	1600	900	778	790	143	159	16
E66522	1700	800	678	688	143	159	18
E66523	1800	800	678	688	143	159	18

largeur du receveur (mm)	X	Y	Z
700	40	11	51
800	40	18	58
900	40	16	56

