



	E6D126	E6D127	E6D128	E6D129
Mm	1200	1400	1200	1400
A mini/maxi	1164/1200	1364/1400	1164/1182	1364/1382
Mm			800	900
B mini/maxi			764/782	864/882
C	1050	1250	1050	1250
D	556	656	590	690
E	510	610	510	610

