

Features

- Brass construction
- Durable KOHLER finishes resist corrosion and tarnishing
- Optimized sprayface and large nozzles with Katalyst® Air-induction for improved water coverage
- Leak-free ceramic disc valve with lifetime warranty
- Includes 8" ultra thin round Katalyst Air Rainhead
- Includes 110 mm Renew Organic 3-function handshower
- Adjustable inlet fittings with 15 mm tolerance

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552
- GB 18145-2014
- EN 817-2008


Installation Notes

Install this product according to the installation guide.


Specified Model

Model	Description	Color/Finished
K-97826T-4	Aleo shower column	CP: Polished Chrome

For a full range of color finishes in your market please contact your local Kohler representative



Flow Curve Handshower




Flow Curve Showerhead

Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลิตภัณฑ์ของเหลือ
- วัสดุเคลือบผิวพิเศษจากโคโธเลอร์ คงทน งาม
- หัวผักบัวพร้อมรูกักบัวขนาดใหญ่แบบเรียงตัว ระบบแคตตาลิสเทคโนโลยีการอัดอากาศเพื่อส่ายน้ำชุ่มฉ่ำเต็มสัมผัส
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- พร้อมหัวผักบัวแคตตาลิสทรงกลมบางพิเศษขนาด 8 นิ้ว
- พร้อมผักบัวสายอ่อน รีโนว-ออกานิค ขนาด 110 มม. ปรับส่ายน้ำได้ 3 ระดับ
- อุปกรณ์ติดตั้งกับท่อน้ำเข้าปรับระยะได้ 15 มม.

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552
- GB 18145-2014
- EN 817-2008


ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้เครื่องมือแนะนำการติดตั้ง


รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-97826T-4	ก๊อกลสมยีนอาบพริ้วมชุดผักบัวสายอ่อนและชุดผักบัวก้านแข็งแบบทำมม 90 องศา รุ่นอาเลโอ	CP: สีโครเมอ

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน



กราฟแสดงอัตราการไหล ผักบัวสายอ่อน




กราฟแสดงอัตราการไหล ผักบัวก้านแข็ง

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



หมายเหตุ: ระยะเวลาแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์

