

Features

- Solid metal construction
- Durable KOHLER finishes resist corrosion and tarnishing
- Flexible G1/2" supply hoses for easy installation
- Leak-free ceramic disc valve with lifetime warranty
- Coin aerator allows for easy cleaning and maintenance
- Metal mounting hardware assures a secure installation
- Includes pop-up drain
- 100 mm spout reach (K-74013T-4)
- 120 mm spout reach (K-74026T-4)
- Lever handle
- Compliments most Kohler product lines

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2067-2552
- GB 18145-2014


Installation Notes

Install this product according to the installation guide.


Specified Model

Model	Description	Color/Finished
K-74013T-4	Taut single-hole lavatory faucet	CP: Polish chrome
K-74026T-4	Taut tall single-hole lavatory faucet	CP: Polish chrome

For a full range of color finishes in your market please contact your local Kohler representative.



Flow Curve For K-74013T-4




Flow Curve For K-74026T-4


Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.

Unit: mm



K- 74013T-4



K-74026T-4

Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลิตจากโลหะ
- วัสดุเคลือบผิวพิเศษของโคห์เลอร์ คงทน เงางาม
- สายน้ำดีขนาด G1/2 นิ้ว ติดตั้งง่าย
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- ทำความสะอาดปากก๊อกได้ง่าย โดยใช้เหรียญไขเปิดปากก๊อก
- ชุดอุปกรณ์ติดตั้งโลหะ มั่นคง แข็งแรง
- พร้อมส่ดืออ่างแบบป๊อปอัพ
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 100 มม. (K-74013T-4)
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 120 มม. (K-74026T-4)
- มือบิดแบบก้านโยก
- เหมาะกับผลิตภัณฑ์ส่วนใหญ่ของโคห์เลอร์

มาตรฐาน

คุณสมบัติตามมาตรฐาน :

- มอก. 2067-2552
- GB 18145-2014


ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง


รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-74013T-4	ก๊อกผสมอ่างล้างหน้ารูเดี่ยวแบบก้านโยก รุ่นทอช	CP: สีโครมเงา
K-74026T-4	ก๊อกผสมอ่างล้างหน้าทรงสูงรูเดี่ยวแบบก้านโยก รุ่นทอช	CP: สีโครมเงา

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน



กราฟแสดงอัตราการไหล สำหรับ K-74013T-4




กราฟแสดงอัตราการไหล สำหรับ K-74026T-4


หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



K-74013T-4



K-74026T-4

หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์