


Features

- Vitreous china
- Elongated bowl
- Dual Flush system 3/3.8 liter per flush
- Rimless design
- Auto open/close seat (antibacterial seat) and adjustable thermal warming
- Bidet functionality with stainless steel (front wash, rear wash)
- Heated seat/Deodorizer/UV sanitizing/Dryer
- Wireless LCD with Touch Button Remote Control
- Electrolyzed water
- Night light
- Emergency manual Flush during power outage
- 305 mm rough-in for S-trap
- 700 x 418 x 523 mm

Technical Information

Fixture:	
Configuration	Onepiece, elongated
Water per flush	3/3.8 liter
Passageway	51 mm
Water area	220 x 158 mm
Water depth from rim	136 mm
Water supply pressure	0.07 Mpa - 0.74 Mpa
Electrical power	220V, 50Hz, 1080W
Power Cord Length	About 1.5 m
Ambient temperature	1~40 °C

ONE-PIECE INTELLIGENT TOILET K-77795X



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1
- TIS 792-2554

Required Electrical Service

Dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI) or Earth Leakage Circuit Breaker (ELCB):

GFCI/ELCB	220-240 V, 10 A, 50/60 Hz
-----------	---------------------------

Installation Notes


Install this product according to the installation guide.

Specified Model

Model	Description	Color/Finished
K-77795X-EX	EIR intelligent toilet (White)	0: White
K-77795X-EXSG	EIR intelligent toilet (Sunrise Gold)	0: White
K-77795X-EXRGD	EIR intelligent toilet (Rose Gold)	0: White

Dimensions are approximate.

Unit: mm




Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- สุขภัณฑ์เซรามิกประเภทวิเทียสไชน่า (Vitreous china)
- โถสุขภัณฑ์แบบหน้ายาว
- ระบบชำระล้างดูอัลฟลัช 3/3.8 ลิตร
- ดีไซน์โถแบบไร้ขอบ
- ฝารองนั่งป้องกันการเกิดแบคทีเรีย พร้อมระบบเปิด-ปิดอัตโนมัติและระบบปรับอุณหภูมิ
- ระบบฉีดชำระในตัว ด้วยก้านฉีดชำระสแตนเลส (ฉีดชำระด้านหน้า/ฉีดชำระด้านหลัง)
- ระบบอุ่นสำหรับที่รองนั่ง/ระบบดับกลิ่นอัตโนมัติ/ระบบฆ่าเชื้อด้วยแสง ยูวี/ระบบเป่าลมแห้ง
- รีโมทคอนโทรลแบบไร้สาย พร้อมหน้าจอ LCD ระบบสัมผัส
- ระบบฆ่าเชื้อโรคด้วยน้ำอเล็กโทรไลต์
- พร้อมไฟกลางคืน
- สามารถกดชำระได้ในกรณีไฟฟ้าดับ
- ระยะจุดกึ่งกลางท่อน้ำทิ้งถึงผนัง 305 มม. สำหรับการติดตั้งท่อน้ำทิ้งลงพื้น
- 700 x 418 x 523 มม.

สุขภัณฑ์ขึ้นเดียว พร้อมระบบชำระล้างอัตโนมัติ K-77795X



ข้อมูลผลิตภัณฑ์

ข้อมูลอ่างอาบน้ำ	
ลักษณะ	สุขภัณฑ์ขึ้นเดียว, หน้ายาว
การใช้น้ำชำระล้างต่อครั้ง	3/3.8 ลิตร
ขนาดท่อน้ำทิ้ง	51 มม.
ผิวหน้า	220 x 158 มม.
ความลึกจากขอบโถสุขภัณฑ์ถึงผิวหน้า	136 มม.
แรงดันน้ำ	0.7~7.4 เมกะปาสคาล
ระบบไฟฟ้า	220 โวลต์, 50 เฮิร์ตซ์, 1080 วัตต์
ความยาวของสายไฟ	ประมาณ 1.5 ม.
อุณหภูมิแวดล้อม	1~40 องศาเซลเซียส

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ASME A112.19.2/CSA B45.1
 - มอก. 792-2554

ระบบไฟฟ้าที่จำเป็น

ติดตั้งอุปกรณ์ตัดกระแสไฟฟ้าอัตโนมัติแบบ GFCI (Ground-Fault Circuit-Interrupter) หรือ ELCB (Earth Leakage Circuit Breaker)	
GFCI/ELCB	220-240 โวลต์, 10 แอมป์, 50/60 เฮิร์ตซ์


ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง


รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-77795X-EX	สุขภัณฑ์แบบขึ้นเดียว รุ่นแอร์	0: สีขาว
K-77795X-EXSG	สุขภัณฑ์แบบขึ้นเดียว รุ่นแอร์ (ขอบสีโครมโรสโกลด์)	0: สีขาว
K-77795X-EXRGD	สุขภัณฑ์แบบขึ้นเดียว รุ่นแอร์ (ขอบสีโรสโกลด์)	0: สีขาว

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



ด้านหน้าของโถสุขภัณฑ์



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์