

TH3 WAY COLUMN W/MF SHOWERHEAD K-23861T

Features

- Durable Kohler finishes resist corrosion and tarnishing
- Adjustable inlet fittings with 10 mm tolerance
- Intuitive control by one touch of a button changes water outlet and water volume
- Precise thermostatic temperature control with over-ridable temperature stop
- Extra-large control panel serves as an stylish and useful storage shelf
- Includes bath outlet
- Includes 2-function showerhead
- Includes 3-function handshower

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552
- GB/T 23447-2009

Installation Notes


Install this product according to the installation guide.




Specified Model

Model	Description	Color/Finished
K-23861T-9	Urbanity+ thermostatic shower column	CP: Polished Chrome


For a full range of color finishes in your market please contact your local Kohler representative.



Flow Curve (Bath outlet)




Flow Curve (Showerhead)



Flow Curve (Handshower)

Note: Flow rate are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.
Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- วัสดุเคลือบผิวพิเศษจากโคห์เลอร์ คงทน เงางาม
- อุปกรณ์ติดตั้งกับท่อน้ำเข้าปรับระยะได้ 10 มม.
- การควบคุมที่ใช้งานง่ายเพียงปุ่มเดียวสำหรับเปลี่ยนช่องจ่ายน้ำและปริมาณน้ำ
- ระบบเทอร์โมสแตตติกควบคุมอุณหภูมิแม่นยำ พร้อมตัวหยุดนิรภัย
- แผงควบคุมขนาดใหญ่พิเศษทำหน้าที่เป็นชั้นวางของที่มีสไตล์และมีประโยชน์
- พร้อมปากก๊อกอ่างอาบน้ำ
- พร้อมฝักบัวก้านแข็งปรับสายน้ำได้ 2 ระดับ
- พร้อมฝักบัวสายอ่อนปรับสายน้ำได้ 3 ระดับ

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552
- GB/T 23447-2009

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

ก๊อกผสมลงอ่างอาบน้ำและยืนอาบ พร้อมชุดฝักบัวสายอ่อนและชุดฝักบัวก้านแข็ง




K-23861T



รุ่นผลิตภัณฑ์


รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-23861T-9	ก๊อกผสมลงอ่างอาบน้ำและยืนอาบระบบเทอร์โมสแตตติกพร้อมฝักบัวสายอ่อนและชุดฝักบัวก้านแข็ง รุ่นเออร์เบนิที+	CP: สีโครมเงา

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน



หมายเหตุ: อัตราการไหลโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ
 หน่วย: มม.



หมายเหตุ: ระยะเวลาแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์