

Features

- Brass construction
- Precise thermostatic control with over-ridable temperature stop
- Durable KOHLER finishes resist corrosion and tarnishing
- Spout Reach 131 mm
- Side control handles
- Adjustable inlet fittings with 15mm tolerance
- Includes Rain Duet push button, 3 function handshower
- Katalyst air-induction technology for powerful and even coverage

EXPOSED WALL MOUNT THERMOSTATIC FAUCET

K-97386T

ALSO K-97384T



Codes/Standards Applicable

- GB 18145-2014 • EN 817-2008
- GB/T 23447-2009 • QB 2806-2006
- EN 1111-1998


Installation Notes

Install this product according to the installation guide.


Specified Model

Model	Description	Color/Finished	
K-97386T-9	Avid Exposed Wall Mount Thermostatic Bath Shower Faucet	<input type="checkbox"/> Polished Chrome (CP)	<input type="checkbox"/> Titanium (TT)
K-97384T-9	Avid Exposed Wall Mount Thermostatic Shower Only Faucet	<input type="checkbox"/> Polished Chrome (CP)	<input type="checkbox"/> Titanium (TT)

For a full range of color finishes in your market please contact your local Kohler representative.







Flow Curve – Bath Spout




Flow Curve – Handshower

Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)


Dimensions are approximate.
Unit: mm



97386T-9



K-97384T-9



Product Diagram