

COMPOSED

Features

- · Brass construction
- · Leak-free ceramic disc valve with lifetime warranty
- · Durable KOHLER finishes resist corrosion and tarnishing
- Flexible G1/2" supply hoses for easy installation
- · Directionally adjustable, laminar-flow aerator
- · Spout reach 151 mm
- · Joystick handle
- · Includes pop-up drain

SINGLE CONTROL
LAVATORY FAUCET

K-73158T

ALSO K-73053T AND K-73057T



Codes/Standards Applicable

• GB 18145-2014

• EN 817-2008

• TIS 2067-2552

EN 200-2008


Installation Notes

Install this product according to the installation guide.

Specified Model

Model	Description	Color/Finished		
K-73158T-4	Composed Single Control Lavatory Faucet	☐ Polished Chrome (CP)	☐ French Gold (AF)	☐ Titanium (TT)
K-73053T-4	Composed Single Control Tall Lavatory Faucet	☐ Polished Chrome (CP)	☐ French Gold (AF)	☐ Titanium (TT)
K-73057T-4	Composed Single Control Super Tall Lavatory Faucet	☐ Polished Chrome (CP)	☐ French Gold (AF)	☐ Titanium (TT)


For a full range of color finishes in your market please contact your local Kohler representative.



Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.


Unit: mm




Product Diagram









K-73057T-4