

### Features

- Vitreous china.
- Elongated bowl.
- Concealed bowl.
- Includes Quiet close seat.
- Includes polished chrome push button.
- Wash Down flushing system.
- Dual flush 3/4.5 liter per flush.
- 185 mm rough-in for Plastic P-trap(K-28413H-\*\*).
- 65 mm rough-in for Plastic S-trap(K-28414H-\*\*).
- 700 x 391 x 776 mm


### Codes/Standards Applicable

Specified model meets or exceeds the following:

- BS:EN 997

### TWO-PIECE TOILET WITH SEAT

## K-28413H ALSO K-28414H



### Technical Information

Fixture:	
Configuration	two-piece, elongated
Water per flush	3/4.5 liter
Passageway	51 mm
Water area	127 x 102 mm
Water depth from rim	240 mm
Seat post hole centers	140 mm

Included Components:	
Bowl(For K-28413H-**)	28412H-**
Bowl(For K-28414H-**)	29759H-**
Tank	22243H-**
Tank cover	1203722-SP-**
Quiet close seat	K-3857K-**
Plastic P-Trap(For K-28413H-**)	1138552
Plastic S-Trap(For K-28414H-**)	1353009

### Specified Model

Model	Description	Color/Finishes
K-28413H	Reach Concealed two-piece toilet 3/4.5L, P-trap 185 MM, with Quiet close seat	0: White
K-28414H	Reach Concealed two-piece toilet 3/4.5L, S-trap 65 MM, with Quiet close seat	0: White


### Installation Notes

Install this product according to the installation guide.

Recommended Accessories		
1065832	Water Supply Hose, Stainless	CP: Polished Chrome
1265885-SP	Shut Off Valve	CP: Polished Chrome

Dimensions are approximate. (Do not direct measure a dimensional from picture below)

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at anytime without notice.

### Product Diagram