

MAXISPACE 博纳 INSTALLATION INSTRUCTIONS 安装说明书 MIRRORED CABINET 镜柜 K-96106T-R/K-96106T-L/K-96107T

BEFORE YOU BEGIN


- Please read these instructions carefully to familiarize yourself with the required tools, materials, and installation sequences. Follow the sections that pertain to your particular installation. This will help you avoid costly mistakes. In addition to proper installation, read all operating and safety instructions.
- All information in these instructions is based upon the latest product information available at the time of publication. Kohler China. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.
- These instructions contain important care, cleaning, and warranty information-please leave instructions for the consumer.
- Before installation carefully inspect the new fixture for any signs of damage.
- This product complies with GB/T10357.4-2013, GB/T10357.5-2013 and GB24977-2010.
- WARNING: Risk of injury or product damage. Be careful when opening the door to avoid pinching fingers.
- WARNING: Don't use acidic or alkalic cleaners or alcohol to clean the surface. Use a dampened cloth to clean.
- CAUTION: Risk of electric shock. Electrical wiring may need to be relocated.
- CAUTION: Risk of property damage. Use anchors (not provided) rated for the loaded weight of this product. Refer to the anchor manufacturer's instructions.
- Important Information: This cabinet is designed for either right or left door swing. Check the wall cavity for obstructions.

安装之前

- 请仔细详阅本指引,以便熟悉所需工具、物料及安装程序。请遵照适用的章节来安装本产品,以免安装失当导致不必要的损失。除了有关正确的安装方法之外,还务请详阅所有操作及安全指引。
- 本指引所载之一切资料,均以印刷时所有之最新产品情况 为基础,科勒中国保留权利随时更改产品特性、包装或供 应情况,恕不另行通知。
- 本指引也包含了有关保养、清洁及担保等重要资料-请交予 用户保存。
- 安装之前,仔细检查产品是否有损伤。
- 本产品符合GB/T10357.4-2013、GB/T10357.5-2013和 GB24977-2010。
- 警告:可能有人员伤害或者产品损坏的危险。为防止门 左右移动时夹到手指,请注意推门的位置。
- 警告:表面不能用含酸或碱性的清洁剂以及酒精清洁, 请用潮布清洁。
- ⚠️警告:触电风险。可能需要重新布线。
- 警告: 财产损失风险。请使用可承载本产品重量的膨胀螺栓(不随货提供)。请参考螺栓制造商的产品说明。
- ▲ **重要信息**:本镜柜有适用于左右开门安装的型号,请注 意区别。请检查墙体内壁空间是否存在障碍物。

ZHONGSHAN KOHLER SHOWER CO., LTD. NO13-1, XINYE ROAD, ZHONGSHAN TORCH DEVELOPMENT ZONE, ZHONGSHAN, GUANGDONG, CHINA POST CODE: 528437 中山科勒卫浴有限公司 广东省中山市中山火炬开发区兴业路13-1号 邮编: 528437

© Copyright Kohler China Investment Co., Ltd. 2017 © 版权为科勒(中国)投资有限公司所有 2017




Kohler reserves the right to change marked dimensions without prior notice. 科勒公司保留随时变更图中标示尺寸的权利,无需另行通知。

Item 序号	Electrical Function 电器功能	Type Descripetion 规格描述	Fixate Place 安装位置
1	Defogger 防雾膜	Input: 220V 50Hz, Pmax=30W	Back of outer-mirror 贴外镜背面
2	Lighting 灯具	Input: 220V 50Hz, Pmax=6W, LED 3000K	Top of inner cabinet 柜内顶部
3	Power Outlet 电源插座	Input: 220V 50Hz, 10A	Bottom of inner cabinet 柜内底部


CABINET INSTALLATION

柜体安装




INSTALLATION


安装



Install mounting bar. Take out the mounting bar and put level. Drill holes according to the hole spaces. 安装托条,拿出托条,水平放置,按托条上的孔距进行钻孔。



STEP




Adjust the door (only necessary if the door does not completely match the cabinet when it is closed). 调门体(当关门时门体和柜体不完全重合时,才需要调节)。


Door adjustments 门的拆装及调整

Remove the hinge cover or the blumotion before adjustion, see Fig A. 调节前取下铰链盖或者阻尼器。见图A。


Adjust the hinge of door in 3 directions to make sure the door level as shown in Fig.B. 门板的三向调节见图B。




Assemble 铰链盖拆卸




Assemble 阻尼器安装 Fig. A 图A



Removal 阻尼器拆卸




Height Adjustment 调节高度



Side Adjustment 调节侧面

Fig. B 图B



Depth Adjustment 调节深度




Install glass shelf 装玻璃层板


- 1. Insert the snap-in pins into the side holes.
- 1. 将嵌入式层板架插入两边侧孔。
- 2. Insert the glass shelf into the snap-in pins. as shown in the left illustration.
- 2. 将玻璃层板插入层板架。如下图安装方式一。
- 3.In case the door opening angle is not enough, insert the glass shelf vertically upwards and then rotate to horizontal position, as shown in the right illustration.

3.如果门打开角度较小,按安装方式一不好装玻璃层板时,可按安装方式二,垂直往上穿入,再旋转水平后推入。




Method Two 安装方式二






Adjust magnifying glass. 调整放大镜


To adjust mirror height, slide up or down. IMPORTANT! Rotate mirror in before closing the door. 上下滑动,以调节镜子高度。 重要:必须在柜门关闭前旋入镜子。





Connect to power line 电源线接入

- 1. Open the wire box and pull out the terminal block.
- 1. 电源线接入前将接线盒打开,把接线端子往上提出。
- 2. Put the terminal block back after connecting the power lines and then close the wire box.
- 2. 电源线接好后,再将接线端子装回,合上接线盒盖。



Note:

- 1. LED light will be brighter when cabinet door is closed and dimmer when cabinet door is open.
- 2. A separated switch is needed for lighting.
- It is recommended to arrange a separated power line for the socket to keep it power on all the time. Power line shall be copper core > 1.5m².
- Power of the electrical equipments connected to the socket shall not exceed 2000w.
- 注:
- 1. 灯具为感应LED灯,关门时亮度增加,打 开时亮度减少。
- 灯具需要用户另外配单独的电源开关,控制灯具的亮灯或熄灯。
- 电源插座的电源线建议单独接线,以保持 常通电的状态。外接电线规格为大于或等 于1.5平方铜芯线。
- 4.电源插座外接电器总功率不能超过2000W.

STEP 8