

Features

- *Katalyst Air-Induction technology for powerful and even coverage*
- *Durable KOHLER finishes resist corrosion and tarnishing*
- *Robust wall mounting system and hardware*
- *3-function showerhead - Cascade, Rain and Laminar*
- *Integrated warm white lights powered by the flow of water*

WALL MOUNT SHOWERHEAD K-72830-L-CP



Codes/Standards Applicable

- Specified model meets or exceeds the following:
- GB/T 23447-2009


Installation Notes

Install this product according to the installation guide.

Specified Model


Model	Description	Color/Finished
K-72830T-L-CP	Beitou Wall Mount Showerhead	Polished Chrome (CP)

For a full range of color finishes in your market please contact your local Kohler representative.



- Note: 1. Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)
 2. Flow curve above shows single outlet flow rate using supplied flow regulator.
 3. Suggested minimum supply system capacity: 13 LPM.
 For simultaneous showerhead functionality, higher system flow rate required.

Dimensions are approximate.
 Unit: mm



Product Diagram