

Features

- Vitreous China
- Without Overflow
- Rectangular Design
- Above counter
- Only Drain cutting (no profile cutting required)



Recommended Accessories

- Bottle Trap (75823IN)
- Drain (24740IN)

COMPATIBLE FAUCETS	
PRODUCT DESCRIPTION	SKU CODE
Aleo Single Control Pillar Lavatory Faucet	72288IN-4-CP
Kumin Pillar Lavatory Faucet	99452IN-4-CP
Aleo+ Single Control Pillar Lavatory Faucet	72326IN-4-CP
Fairfax Pillar Lavatory Faucet	11549IN-4-CP
Cuff Pillar Lavatory Faucet	37308IN-4-CP
Purist Single Control Lavatory Faucet	14402IN-4A-CP
Fairfax Lavatory Faucet	8657IN-CP
Symbol Lavatory Faucet	19480IN-CP
Aleo Lavatory Faucet	72275IN-4-CP
Taut Lavatory Faucet	74013IN-4-CP
Composed Lavatory Faucet	73158IN-4-CP
Stance Lavatory Faucet	14760IN-4ND-CP
Aleo+ Lavatory Faucet	72312IN-4-CP
Beitou Lavatory Faucet	99856IN-4-CP
Eolia Lavatory Faucet	8620IN-ND-CP
Sirocco Lavatory Faucet	8611IN-1ND-CP
July Lavatory Faucet	16027IN-4ND-CP



KOHLER® Ten-Year Limited Warranty

See website for detailed warranty information.

Available Color/ Finishes

Color tiles intended for reference only

Color	Code	Description
	0	White



Notes

Install this product according to the installation instructions.

Product does not have an overflow.

*Spout must be 3.9" (99mm) long (min) for adequate clearance into the bathroom sink.

Technical Information

All Product Dimensions are nominal

Lavatory configuration	Single
Installation	Above Counter
Bowl area	Length: 23 5/8" (600 mm) Width: 17 5/16" (440 mm) Height: 5 15/16" (150 mm) Depth: 4 15/16" (125 mm)
Drain hole	Ø41.65 - 46.5 mm
Template	1301458IN-7